

Product type designation	RUGGEDCOM RX5000PN LM 4CG01 LINE MODULE 4X 10/100/1000TX RJ45
Suitability for operation	RX5000
Interfaces	
Number of electrical/optical connections / for network components or terminal equipment / maximum	4
Number of electrical connections <ul style="list-style-type: none"> • for network components or terminal equipment / maximum 	4
Number of 10/100/1000 Mbit/s RJ45 ports	4
Type of electrical connection <ul style="list-style-type: none"> • for network components or terminal equipment 	RJ45
Permitted ambient conditions	
Ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • Note 	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C A maximum ambient operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP40
Design, dimensions and weight	
Design	Media module
Width	40 mm
Height	180 mm
Depth	240 mm
Net weight	1 kg
Coating	no
Mounting type <ul style="list-style-type: none"> • Installation in media module slot 	screwed Yes
Standards, specifications, approvals	
Standard <ul style="list-style-type: none"> • for EMC • for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference 	FCC Part 15 (Class A), EN55022 (CISPR22 Class A) UL 60950-1, CSA C22.2 No. 60950-7 Hazardous Locations: Class 1 Division 2 EN 61000-6-4 (Class A)

<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2
Certificate of suitability	EN 61000-6-2, EN 61000-6-10
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • C-Tick 	No
<ul style="list-style-type: none"> • KC approval 	No
<ul style="list-style-type: none"> • E1 approval 	No
<ul style="list-style-type: none"> • Railway application in accordance with EN 50155 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50124-1 	Yes
<ul style="list-style-type: none"> • IEC 61850-3 	Yes

Further Information / Internet Links

Internet-Link

- | | |
|--|---|
| <ul style="list-style-type: none"> • to website: Industry Mall/RUGGEDCOM selector | http://ruggedcom-selector.automation.siemens.com |
| <ul style="list-style-type: none"> • to website: Siemens RUGGEDCOM | http://siemens.com/ruggedcom |
| <ul style="list-style-type: none"> • to website: Selector for cables and connectors | http://www.siemens.com/snst |
| <ul style="list-style-type: none"> • to website: Industrial communication | http://www.siemens.com/simatic-net |
| <ul style="list-style-type: none"> • to website: Industry Mall | https://mall.industry.siemens.com |
| <ul style="list-style-type: none"> • to website: Information and Download Center | http://www.siemens.com/automation/net/catalog |
| <ul style="list-style-type: none"> • to website: Image database | http://automation.siemens.com/bilddb |
| <ul style="list-style-type: none"> • to website: CAx Download Manager | http://www.siemens.com/cax |
| <ul style="list-style-type: none"> • to website: Industry Online Support | https://support.industry.siemens.com |

last modified:

16.03.2015