

Ultrasonic transit time Sensor Clamp-On, Universal Size D2, pair, dedicated, Ex Zone 0,1,2, Class 1, Div 1,2, any pipe materials, Liquid, Pipe Diameter range 152 - 610 mm (6 - 24"), Temperature -40C - +121C (-40F - +250F)  
Housing Polyetherimide/StSt corrosion resistant, for FST020, FST030, (substitute for FUx1010)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.de/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com>