

Cable VGA Splitter 2 Port



Specifications

- Supports SVGA, VGA, XGA and multisync monitors
- Bandwidth 450 MHz
- Resolution 2048 x 1536 in 24 or 32 bit true color mode
- Transmission range up to 55m
- Cascadable (daisy-chain)
- Supports Windows 98SE / ME / 2000 / XP and Mac OS
- No driver required
- LED to indicate power on/off
- Power supply DC 5V via USB-Y-cable from USB port
- Enclosure: plastic
- Color: black
- Dimensions: 70 x 25 x 72 mm
- Weight: 0.124 kg

Package contents

- Cable VGA Splitter 2 Port
- User Manual



Connectors

- 1 x HDB 15/M (VGA in)
- 2 x HDB 15/F (VGA out)
- 1 x USB Type A/M (power)
- 1 x USB Type A/F
- Cable length (VGA in): 0.15m
- Cable length (USB): 0.40m
- Power supply: DC 5V from USB port