



## MHDBC-Series – D-Crimp Connectors

### Material Specification:

- Insulator: Glass filled Polyester, Black  
UL94 V-0
- Shell: Stamped Steel, Tin Plated
- Contacts: Copper Alloy, Stamped & Formed Pins  
100 inserts min.
- Contact Plating: Selective Gold over Nickel



Size	A	B	C	E	F	G
9	16,33	24,99	30,81	16,92	11,08	8,31
15	24,66	33,32	39,14	25,25	19,39	16,62
25	38,38	47,04	53,04	38,96	33,24	30,47
37	54,84	63,50	69,32	55,25	49,86	47,09
50*	Available on request					

### Order Codes:

Plug Connector		
09	2101-0190-01	MHDBC09-SP
15	2101-0190-02	MHDBC15-SP
25	2101-0190-03	MHDBC25-SP
37	2101-0190-04	MHDBC37-SP
50	On request	

Socket Connector		
09	2101-0190-11	MHDBC09-SS
15	2101-0190-12	MHDBC15-SS
25	2101-0190-13	MHDBC25-SS
37	2101-0190-14	MHDBC37-SS
50	On request	

### Order Codes - CRIMP Contacts, AWG 24-28:

Crimp Contacts on REEL - 5000pcs		
Male Contacts	2101-0199-01	MHDBCTMR
Female Contacts	2101-0199-11	MHDBCTFR

Other AWG available on request

