

### THB.387.D5A

TeePlug Powersocket 5 pole Screw terminal with female contacts , 4 mm max conductor size IP65 17.5A 450V 1 cable entry



#### SPECIFICATION

Type	Socket
Cable Entries	1
Number of Poles	5
Terminal Type	Screw
Body Material	PA66
IP Rating	65
Max Conductor Size (Sq mm)	4
Max Current (A)	17.5
Max Voltage (V)	450
Minimum Temp Rating °C	-40
Max Temp Rating °C	125
Fixing System	Chassis
Temperature "T" Rating	T125