

product: DELPHI PN 15326269

material: CUSN3ZN9

VERSION I

surface: SN

material thickness: 0,30 mm

cross section [mm²]: 0,75 | 1,0

strip length: 4,60 mm

cable type: FLRY-B

insulation ø [mm]: 1,70 - 2,10

seal: DPN 15366060

**Uncontrolled
Copy**
For Information only!


conductor dimension					crimp dimension [mm]					
cable type	cross sect. [mm ²]	struct. n x d [mm]	insul. diam. [mm]	tear-out force [N]	core		insulation			
					height ± 0,05	width ± 0,10	height ± 0,10	width ± 0,10	height ± tol.	width ± tol.
FLRY-B	0,75	24 x 0,21	1,80	120	1,25	2,10	3,30	3,50		
FLRY-B	1,0	32 x 0,21	2,00	160	1,40	2,10	3,40	3,50		

core:
C-2.00-3.5-15
DPN 10713754


insulation:
IS-008
DPN 10714462

anvil:
ASR-2.00-3.50-8.5-3.4-1.0
DPN 10783491

two piece anvil:
AC-2.00-3.75
DPN 10803507
AI-3.50-4.6-1.0
DPN 10805969




DELPHI PN 15326269



cable:
 $0,75 \text{ mm}^2 = 24 \times 0,21 \text{ mm}$

crimp height:
1,25 mm

crimp width:
2,10 mm



cable:
 $1,00 \text{ mm}^2 = 32 \times 0,21 \text{ mm}$

crimp height:
1,40 mm

crimp width:
2,10 mm