


- ELECTRICAL TEST:
- 1.100% OPEN SHORT SHORT & MIS WIRE TEST
 - 2.CONTACT RESISTANCE:2 OHM(MAX)
 - 3.INSULATION RESISTANCE:10M OHM(MIN)
 - 4.HI-POT TEST:DC 300V/10ms

PIN Assignment



17	A10-R042395	W*L=20*55MM COPPER FOIL	1	pcs
16	A6-0000099	Display/Port M DUST CAP	1	pcs
15	A6-R104378	Display/Port M(DP01#)ABS UP SHELL SNOW WHITE	1	pcs
14	A6-R104377	Display/Port M(DP01#)ABSTOP SHELL SNOW WHITE	1	pcs
13	A2-R021284	Display Port Male Pin Gold,Insulation Black,Shell Gold Plated	1	pcs
12	A6-0000157	mini Display Port M DUST CAP	1	pcs
11	A6-R104239	mini DisplayPort(solder) M ABS UP SHELL SNOW WHITE	1	pcs
10	A6-R104240	mini DisplayPort(solder) M ABS TOP SHELL SNOW WHITE	1	pcs
9	A10-R075143	H.S.T.: φ1.5*22mm BLACK	1	pcs
8	A10-R075147	H.S.T.: φ1.0*10mm BLACK	5	pcs
7	A10-R065324	H.S.T.: φ2.0*8MM BLACK	5	pcs
6	A5-R047107	45P SNOW WHITE PVC料	10	9
5	A5-R047011	PE	3	9
4	A6-R021133	mini Display Port M Back shell nickel plated	1	pcs
3	A6-R021212	mini Display Port M Front shell gold Plated	1	pcs
2	A2-R021292	mini Display/Port M Insulation:WHITE PIN Gold plated, With PCB	1	pcs
1	A4-R001678	Display Port UL20276 [32AWG(7/0.08TC)*1PR+EAM]*5+32AWG(7/0.08TC)*5C+D(BC)+AB 85% (16/7/0.12AL) OD:4.8MM SNOW WHITE	1	m

REV.	TOLERANCE	DESCRIPTION	DATE
	INCHES M/M		
.X	.015		
.XX	.010		
.XXX	.005		
TITLE:		MINI DP M TO DP M 1M GOLD	
CUSTOMER :		CD	
CUSTOMER P/N :		CDLMDP-100	
SCALE	NONE		REV.
UNIT	MM		A
DATE	11.03.23		1/2

NO	DESCRIPTION	Q'TY	UNIT
----	-------------	------	------