

AARDSTKL., BRNZ, SIL BRNZ, 3/8"DIA,#10 2STRND, 6MM SOL-25 MM2  
STRENG

#### CATALOG NUMBER

**CP38**



#### CERTIFICATIONS



#### FEATURES

Voor gebruik met verkoperde aardingsstangen

Parts that are UL 467 Listed are suitable for direct burial in earth or concrete

#### PRODUCTKENMERKEN

Article Number: 158155

Material: Siliciumbrons


Ground Rod Diameter, Nominal: 3/8"

Ground Rod Diameter, Actual: 9,7 mm

Conductor Size: #10 Solid - #2 Stranded;6 mm<sup>2</sup> Solid - 25 mm<sup>2</sup> Stranded

Wrench Size: 3/8"

Torque: 16,90 N-m



### WAARSCHUWING

---

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

**⚠ WAARSCHUWING:** Dit product kan u blootstellen aan chemicaliën waaronder lood, waarvan in de Staat Californië bekend is dat het kanker en geboortefwijkingen of andere reproductieve schade veroorzaakt. Ga voor meer informatie naar [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

#### Noord-Amerika

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europa

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europa

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**