

SVVB clamp holder, positive neutral

For copy and longitudinal face turning using VB indexable inserts

ATORN[®]

Application


For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 72.5°, tip angle 35°, clearance angle 5°
- SVVBN 1212 F11

Advantage

- Very streamlined geometry, optimised for contour lathe work
- Positive geometry for the body ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17836 196
ISO name	SVVB N 2020 K11
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	32 mm
Suitable for indexable inserts	VB.. 1103..
Tool design	Neutral

EAN-Code

4050293563535