

SVHB clamp holder, positive

For copy and longitudinal face turning using VB indexable inserts

ATORN[®]

Application


For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVHBR 1212 F11

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. no.	17836 300
ISO name	SVHB R/L 1212 F11
Shaft height	12 mm
Shank width	12 mm
Length	80 mm
Length of head	13.4 mm
Programming size	16 mm
Suitable for indexable inserts	VB.. 1103..
Tool design	Right

EAN-Code

4050293563351