

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating



Art. no.	22001 158
Brand	ORION
Manufacturer Part Number	22001158
Size	52
Design	Without stem
Profile shape	Round and smooth
Clamping diameter	11 mm
Length	46 mm
Min./max. clamping range diameter	3-52 mm
Gross Weight	0.910 kg
Product Group	2AO

EAN

4053625467662