

Electronic micrometer

With interchangeable ball insert

Mitutoyo

Application:

For measuring e.g. Modules between 0.5–5.25 mm

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65

Advantage:

- IP65

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench, battery



Art. no.	32017 608
Brand	MITUTOYO
Manufacturer Part Number	324-252-30
Display	Digital
Min./max. length measuring range	25-50 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	Hold-function (AE lock), Preset function, ABS function, Automatic switch-off
Min./max. measurement force	5-10 N
Error limit	4 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	45 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	1.180 kg
Product Group	3MA

EAN

4946368695693