

Electronic protractor

Angle 0–180°


ORION[®]

Application:

For measuring 0-180° angles

Execution:

- Mobile measuring arm fixed using knurled thumb screw
- Adjust or set to zero on any flat surface
- 0.05 ° digit increment
- Made of stainless steel
- Error limit $\pm 0.3^\circ$
- Overhead display



Art. no.	38235 015
Brand	ORION
Manufacturer Part Number	38235015
Limb length	200 mm
Degree arc diameter	150 mm
Calibration Group	RD
Gross Weight	0.570 kg
Product Group	3BM

EAN

4053625047901