












Photo	Part number	Description	Target application	MI 2892	MI 2885	MI 2883
	A 1227	1-phase flexible current clamp 3000/300/30 A / 1 V	Single phase flexible current clamp with three selectable measuring ranges. Current clamp is automatically recognized by the instrument. Clamp does not require external power supply as it is powered by the measuring instrument.	•	•	•
	A 1445	1-phase flexible current clamp 3000/300/30 A / 1 V	Single phase flexible current clamp with three selectable measuring ranges. Current clamp is automatically recognized by the instrument. Clamp does not require external power supply as it is powered by the measuring instrument.	•	•	•
	A 1446	1-phase flexible current clamp 6000/600/60 A / 1 V	Single phase flexible current clamp with three selectable measuring ranges. Current clamp is automatically recognized by the instrument. Clamp does not require external power supply as it is powered by the measuring instrument.	•	•	•
	A 1287	1-phase flexible current clamp 3000/300/30 A / 1 V	Single phase flexible current clamp with three selectable measuring ranges. Powered by alkaline or rechargeable batteries.	•	•	•
	A 1037	Current transformer 5 A / 1 V	3-phase transformer for power measurements on distribution panels with 5 A nominal output current.	•	•	•
	A 1354	Temperature probe	Temperature probe can be used for monitoring and recording of temperature trend at measuring objects, such as capacitors, motors, transformers, etc.	•	•	•
	A 1479	Wide range power supply	Wide range power supply (Unom: 85V ÷ 650 Vac / 920 Vdc ) provide power supply directly from voltage measuring terminals. Applicable when standard electrical sockets are not available on measurement site.	•	•	•
	A 1355	GPS receiver	The PQA instrument, current clamps, wide range power supply, 3G/WiFi-Router and GPS are not included in the set.	•	•	
	A 1622	3G / Wi-Fi Router	3G and Wi-Fi Router enables remote handling of the measuring instrument and its data. If the measuring instrument has to be located on distant or hardly accessible place, the 3G and Wi-Fi Router is the only practical solution for fast access to the instrument.	•	•	
	A 1198	Magnetic contact probe	Test probe with magnetic contact provides reliable contact with metal surface during the measurement.	•	•	•
	A 1014	Test probe, black	Test probe with fi 4 mm connection is suitable for performing measurements both in mains outlets and in situations when no schuko outlet is present.	•	•	•

• Option