

## ADAPTOR M12 MALE/ M8 FEMALE 4 POLE CONF. 1,2,3,4

Adapter M12/M8  
for M12 distribution box 4-pole


### [Link to Product](#)

#### Illustration



Male

Female



Product may differ from Image

#### Form

42211

#### Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	Zinc die casting, matte nickel plated
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR

#### General data

Temperature range	-25...+85 °C
-------------------	--------------

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

---

Test isolation voltage	0.8 kVrms
------------------------	-----------

**Commercial data**

---

country of origin	DE
-------------------	----

---

customs tariff number	85369010
-----------------------	----------

---

minimum order quantity	1
------------------------	---