

Han 6 HP EMC-HTE-M25-black



Part number	19 39 006 0406
Specification	Han 6 HP EMC-HTE-M25-black
HARTING eCatalogue	https://b2b.harting.com/19390060406

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HP
Type of hood/housing	Hoods
Description of hood/housing	EMC version

Version

Locking type	Screw locking
Size	6 B
Version	Top entry
Cable entry	1x M25
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	3 Nm
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Commercial data

Packaging size 1

Net weight 233 g

Country of origin China

Customs tariff number 8538900000