


Item no.: 234-502
 Product description: PCB TERMINAL STRIP 2 SOLDER PINS / POLE 2 POLE PIN
 SPACING 2.54 MM / 0.1 IN WITH PUSH BUTTONS



Produkt kann von Bild abweichen / product may differ

Packing unit 600 6*100 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	1.06 g
Color	orange
No. of connection Points	2
No. of potentials	2
pole count	2
Height	14 mm
Height	0.551 in
Width	7.28 mm
Width	0.287 in
Depth	14.4 mm
Depth	0.567 in
Pin spacing from	2.54 mm
Pin spacing from	0.1 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Pollution degree	2

Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 0.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 0.5 mm ²
Cross section to [mm ²]	0.25 mm ²
Cross section to [mm ²]	0.25 mm ²
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
234-502	ABS	04-HG469925/1-PDA	250	4	0,08-0,5
234-502	BV	11915/A0	250	6	0,08-0,5
234-502	CSA	154112-1465035	150	4	28-20
234-502	DNV	E-9215	250	4	0,08-0,5
234-502	GL	17296-00HH	250	4	0,08-0,5
234-502	KEMA	90.6212.01/02	250	6	0,08-0,5
234-502	RMR	11130002	250	4	0,08-0,5
234-502	UR	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected