

Disc 290 TW Wit 1890lm (@6500K) 2700-6500K Ra>80 Tunable White LEDDim

Artikelcode: 606087
 EAN: 7021986060874



Elektrisch

System wattage: 19W
 Spanning: 220-240V

Lichttechniek

Soort lichtbron: LED
 Luminous flux: 1890lm (@6500K)
 Werkzaamheid: 99 lm/W
 Kleurtemperatuur: 2700-6500K
 Kleurweergave (CRI): Ra>80
 MacAdams factor: SDCM: 3
 levensduur: L80/B20>100,000
 Lichtverdeling: Direct
 Optiek: Kunststof opaal prisma
 Bundelhoek: 85°
 UGR: UGR<22

Controle/dimmen

Type: Tunable White LEDDim

Bescherming

Isolatieklasse: Klasse II

Energie en goedkeuringen

Bevat enn lichtbron met energieklasse: E

Materiaal en afwerking

Behuizing: Aluminium
 Kleur: Wit
 Materiaal afdekking: Acrylaat (PMMA)

Montage/Aansluiting



Montage: Opbouw, Binnen
 Aansluiting: Schroefloos klemmenblok

Afmetingen

Hoogte (mm) H: 55
 Diameter (mm) D: 288
 Gewicht (kg) bruto/netto: 2.18 / 1.817

Verpakking

Verpakkingsafmetingen (mm): 295 x 295 x 65



7 0 2 1 9 8 6 0 6 0 8 7 4