

## Nuts

For T-grooves




### Application:

For clamping in T-grooves.

### Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form



<b>Art. no.</b>	<b>26195 080</b>
<b>Type</b>	standard
<b>Nominal dimension of groove</b>	20 mm
<b>Slot nut width</b>	19.7 mm
<b>Thread dimension</b>	M18
<b>Length</b>	32 mm
<b>Height</b>	24 mm
<b>Slot nut height</b>	12 mm
<b>DIN</b>	508

### EAN-Code

4020772080075