



ENGLISH

Datasheet

Constant Voltage LED Driver 24vdc 60 Watt

RS Stock No:176-6727



The RS Pro Range of 60watt Constant voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications

Features:

- Input Voltage 200-240vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 3 Year Warranty
- CE Approved



Specification	
RS Stock No.	1766727
Output Voltage Rating	24vdc
Output Current Range	2.5A
Rated Power	60 Watt
Dimensions	304.6 (l) x 30 (w) x 18 (h) mm
Input Voltage Range	200-240VAC
Input Voltage Frequency	50-60Hz
Inrush Current	0.5A
input power	<75W
Efficiency	88%
Power Consumption Without Load	<0.90
Overload Protection	Hiccup mode, recovers automatically
Short Circuit Protection	Hiccup mode, recovers automatically
Automatically Restart	Yes
Working Temperature	-20°C to +45°C
Relative Humidity	45% to 85%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN6100-3-2, EN61547
Safety Standards	EN61347-1, EN61347-2-13

