




DIN 125 A

~ISO 7089

140 HV

Standard withdrawn



## BN 715

## Flat washers



without chamfer

Steel 140 HV

zinc plated blue



- VSM 13904
- ~UNI 6592
- ~ČSN 021702

M4,5: not included in DIN 125

Article#		d <sub>1</sub>	d <sub>2</sub>	s	
1874861	M1,6	1,7	4	0,3	200
1267582					1000
1875361	M1,7	1,8	4,5	0,3	200
1267590					1000
1879499	M2	2,2	5	0,3	200
1267612					1000
1887416	M2,3	2,5	6	0,5	200
1267639					1000
1777491	M2,5	2,7	6	0,5	200
1777505					1000
1761765					10000
1887440	M2,6	2,8	7	0,5	200
1267655					1000
1887467	M3	3,2	7	0,5	200
1887483					1000
1267663					10000
1887491	M3,5	3,7	8	0,5	200
1267671					1000
1887505	M4	4,3	9	0,8	200
1887513					1000
1267698					10000
1887521	M4,5	4,8	12	1	200
1267701					1000
1887548	M5	5,3	10	1	200
1887556					1000
1267728					5000



M4,5: not included in DIN 125

Article#		d1	d2	s	
1761773	M6	6,4	12	1,6	200
1761781					1000
1761803					5000
1887599	M7	7,4	14	1,6	200
1267744					1000
1761838	M8	8,4	16	1,6	200
1761846					1000
1761862	M10	10,5	20	2	100
1302965					1000
1887793	M12	13	24	2,5	100
1267779					1000
1887807	M14	15	28	2,5	100
1267787					500
1887823	M16	17	30	3	100
1267795					500
1267809	M18	19	34	3	100
1267817	M20	21	37	3	100
1267825	M22	23	39	3	100
1267833	M24	25	44	4	50
1267841	M27	28	50	4	50
1267868	M30	31	56	4	50
3209847	M36	37	66	5	50