



Part no.: 50130697
KD U-M12-3W-V1-030-DP
Connection cable




Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Electrical data

Performance data

Operating voltage	24 V DC ±25%
-------------------	--------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR
No. of pins	3 -pin
Design	Angled
Connector, LED	Yes
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Connection 2

Type of connection	Open end
--------------------	----------

Cable properties

Number of conductors	3 Piece(s)
Wire cross section	0.34 mm ²
AWG	22
Sheathing color	Black
Shielded	No
Silicone-free	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	4.6 mm
Cable length	3,000 mm
Sheathing material	PVC
Wire insulation	PVC
Suitability for drag chains	No
Properties of the outer sheathing	Free of CFC, cadmium, silicone and lead, easily machine-processable
Resistance of the outer sheathing	Good oil, gasoline and chemical resistance, flame retardant in accordance with UL 1581 VW1 / CSA FT1

Mechanical data

Width across flats	13 mm
Bending radius, flexible laying, min.	Min. 10 x cable diameter
Bending radius, stationary laying, min.	Min. 5 x cable diameter

Operation and display

Number of LEDs	1 Piece(s)
----------------	------------

Environmental data

Ambient temperature, operation, flexible use	-5 ... 80 °C
Ambient temperature, operation, stationary use	-30 ... 80 °C

Certifications

Part no.: 50130697 – KD U-M12-3W-V1-030-DP – Connection cable

Degree of protection	IP 65 IP 67
Certifications	c UL US


Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR
No. of pins	3 -pin
Encoding	
Design	Angled
Connector, LED	Yes
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Pin	Conductor color
1	Brown
3	Blue
4	Black



Connection 2	
Type of connection	Open end