


POTENTIAL TERMINAL BLOCK GRAY GRAY YE BL

Potential terminal block
gray/gray/yellow/blue


[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Dimensions H × W × D	70×56×32.5 mm

Temperature range 0...+55 °C (storage temperature -40...+85 °C)

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1