



**M8 female 90° with cable**

PUR 3x0.25 ye UL/CSA+robot+drag chain 10m

M8  
Female 90°  
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.

**[Link to Product](#)****Illustration**

# Female



Product may differ from Image

## Approvals



\* only for products with UL/CSA approved cable

## Form

08081

## Technical Data

|                               |  |
|-------------------------------|--|
| Operating voltage             | max. 60 V AC/DC  |
| Operating current per contact | max. 4 A   |
| Locking of ports              | Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing |
| Protection                    | IP67 inserted and tightened (EN 60529)                           |

**Cables**

|                             |                                  |
|-----------------------------|----------------------------------|
| Cable number                | 050                              |
| No./diameter of wires       | 3 × 0.25 mm <sup>2</sup>         |
| Wire isolation              | PP (br, bl, bk)                  |
| C-track properties          | 10 Mio.                          |
| Torsion                     | 1 Mio. ± 360 °/m                 |
| Jacket Color                | yellow                           |
| Shore hardness outer jacket | 58 ± 3D                          |
| Material (jacket)           | PUR (UL/CSA), welding spark res. |
| Outer diameter              | approx. 4.3 mm                   |
| Bend radius (fixed)         | 5 × outer Ø                      |
| Bend radius (moving)        | 10 × outer Ø                     |
| Temperature range (fixed)   | -40...+90 °C                     |
| Temperature range (mobile)  | -25...+90 °C                     |

**General data**

|                   |  |
|-------------------|--|
| Temperature range | -25...+85 °C, depending on cable quality |
|-------------------|--|

**Commercial data**

|                        |          |
|------------------------|----------|
| country of origin      | DE       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |