

Ultrasonic transit time Sensor Clamp-On, High Precision, Size C2H, pair, dedicated, Ex Zone 0,1,2, Class 1, Div 1,2, for steel pipe, Liquid/Gas, Pipe wall thickness from 5,8 - 8,1 mm (0.23 - 0.32"), Best Temperature >80C (>176F) max. -40C - +121C/-40F - +250F Housing Polyetherimide/StSt corrosion resistant, suggested for FST030, (substitute for FUG1010)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.de/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>