

BD2-AK04/OGB250J-3 TAP-OFF UNIT 250A / 3 POLE

Model		
Product designation		tap-off unit for BD2 busbar trunking system
Protection class		
Protection class IP		IP54
Main circuit		
Operating frequency / Rated value		
• minimum	Hz	50
• maximum	Hz	60
Operating voltage / with AC		
• at 50 Hz / Rated value / maximum	V	400
• at 60 Hz / Rated value / maximum	V	400
Operating current		
• for circuit 1 / with AC / at 50 Hz / Rated value / maximum	A	250
• for circuit 1 / with AC / at 60 Hz / Rated value / maximum	A	250
Connections		
Connectable conductor cross-section / in the outgoing unit		
• minimum	mm ²	6
• maximum	mm ²	150
Tap-off points		
Outgoing unit version		cable entry
Size of the outgoing feeder		04
Number of poles / of the outgoing feeder		5
Mechanical Design		
Height	mm	278
Width	mm	494
Length	mm	725
Product component / Locking mechanism		Yes



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/BVP:611355>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/BVP:611355/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=BVP:611355

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015