

Hexagon Socket Set Screws ISO 4027 (formerly DIN 914) with Cone Point


Material: Steel, black oxide finish, hardness class 45H.
Stainless steel A2, hardness class 21H.



Set screws with fluted cone (dimension d_t).

To use as a grub screw for fixing an element on a shaft.

For a higher retaining force, there should be a countersink made into the shaft.



Ordering Details: e.g.: Product No. 61900305, Set Screw ISO 4027, Steel, M3 x 5mm

Product No. Steel 45H	Product No. Stainless	d mm	l mm	γ °	d_t max. mm	s mm	Weight g
619 003 05	619 103 05	M3	5	90	0,75	1,5	0,17
619 003 08	619 103 08	M3	8	90	0,75	1,5	0,29
619 004 04	619 104 04	M4	4	120	1	2	0,18
619 004 05	619 104 05	M4	5	120	1	2	0,26
619 004 06	619 104 06	M4	6	90	1	2	0,34
619 004 08	619 104 08	M4	8	90	1	2	0,50
619 004 10	619 104 10	M4	10	90	1	2	0,66
619 004 12	619 104 12	M4	12	90	1	2	0,82
619 004 16	619 104 16	M4	16	90	1	2	1,14
619 004 20	619 104 20	M4	20	90	1	2	1,46
619 005 05	619 105 05	M5	5	120	1,25	2,5	0,37
619 005 06	619 105 06	M5	6	120	1,25	2,5	0,49
619 005 08	619 105 08	M5	8	90	1,25	2,5	0,73
619 005 10	619 105 10	M5	10	90	1,25	2,5	0,97
619 005 12	619 105 12	M5	12	90	1,25	2,5	1,21
619 005 16	619 105 16	M5	16	90	1,25	2,5	1,69
619 005 20	619 105 20	M5	20	90	1,25	2,5	2,17
619 005 25	619 105 25	M5	25	90	1,25	2,5	2,77
619 006 06	619 106 06	M6	6	120	1,5	3	0,69
619 006 08	619 106 08	M6	8	90	1,5	3	1,04
619 006 10	619 106 10	M6	10	90	1,5	3	1,39
619 006 12	619 106 12	M6	12	90	1,5	3	1,74
619 006 16	619 106 16	M6	16	90	1,5	3	2,44
619 006 20	619 106 20	M6	20	90	1,5	3	3,14
619 006 25	619 106 25	M6	25	90	1,5	3	4,02
619 006 30	619 106 30	M6	30	90	1,5	3	4,89
619 008 08	619 108 08	M8	8	120	2	4	1,72
619 008 10	619 108 10	M8	10	90	2	4	2,35
619 008 12	619 108 12	M8	12	90	2	4	2,98
619 008 16	619 108 16	M8	16	90	2	4	4,24
619 008 20	619 108 20	M8	20	90	2	4	5,50
619 008 25	619 108 25	M8	25	90	2	4	7,08
619 008 30	619 108 30	M8	30	90	2	4	8,65
619 010 10	619 110 10	M10	10	120	2,5	5	3,41
619 010 12	619 110 12	M10	12	90	2,5	5	4,42
619 010 16	619 110 16	M10	16	90	2,5	5	6,43
619 010 20	619 110 20	M10	20	90	2,5	5	8,44
619 010 25	619 110 25	M10	25	90	2,5	5	10,9
619 010 30	619 110 30	M10	30	90	2,5	5	13,5
619 012 12	-	M12	12	120	3	6	6,1
619 012 16	619 112 16	M12	16	90	3	6	8,9
619 012 20	619 112 20	M12	20	90	3	6	11,7
619 012 25	619 112 25	M12	25	90	3	6	15,3
619 012 30	619 112 30	M12	30	90	3	6	18,8



Loctite® thread locking and bonding products page 1034.