




**Have a Question?**  
Chat with a Product Information Specialist

What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [Support Center](#) [My Account](#)

**926894-3 Product Details**

[Share](#) [Print](#) [Email](#)



**926894-3**

TE Internal Number: 926894-3

**Active**

[View 3D PDF](#)

**.250" Centerline, 600 V, 19 - 36 A max**

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- Contact
- Universal MATE-N-LOK Product Line
- Contact Type = Pin
- Applies To Wire/Cable
- Crimp Termination Method

[View all Features](#)

**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Housings \(206\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

[Buy Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- [UMNL-STIFT \(EINZELAUSFUEHRUNG\)](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:** [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version L)
- [3D Model](#) (IGES, Version L)
- [3D Model](#) (STEP, Version L)

[List all Documents](#)

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)
- [Housings \(206\)](#)

**Product Features (Please use the Product Drawing for all design activity)**

**Product Type Features:**

- Product Type = Contact
- Product Line = Universal MATE-N-LOK
- Insulation Diameter (mm [in]) = 3.30 [.130] Max.

**Electrical Characteristics:**

- High Current = No
- Current Rating (A) = 19
- Voltage (VAC) = 600

**Termination Features:**

- Termination Method = Crimp
- Solder Tail Contact Plating = Pre-Tin

**Body Features:**

- Wire Range (mm [AWG]) = 0.50-2.00<sup>2</sup> [20-14]
- Contact Diameter (mm [in]) = 2.13 [0.084]

**Contact Features:**

- Contact Type = Pin
- Contact Termination Type = Crimp
- Contact Base Material = Phosphor Bronze
- Sealable = No

**Industry Standards:**

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- Applies To = Wire/Cable

**Packaging Features:**

- Packaging Method = Loose Piece

**Other:**

- Brand = AMP

**Corporate Information**

[Who We Are](#)  
[Investors](#)  
[News Room](#)

**Quick Links**

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)

**Customer Support**

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)