

50007M12BSSW

Perfect cable gland with spiral top PA/SW M12/PG 7 thread length 8, min/max cable dia 3-6.5



PRODUCT SPECIFICATIONS

Additional material detail	Body - Polyamide PA6 V-2
Standards	EN50262/UL514B
Product Type	Standard
Sealing ring material	Polychloroprene-Nitrile rubber CR/NBR
Body material	Polyamide
Min temperature °C	-20
Max temperature °C	100
IP rating	68
Colour	Black - RAL 9005
Thread size	M12
Clamping range min (mm)	3
Clamping range max (mm)	6.5
External connecting thread type	Metric
Thread length (mm)	8
Comments	details about tests - see annex
Width across flat 1 (mm)	15
Width across flat 2 (mm)	15
Height (mm)	63.5
Connecting thread size	M12x1.5