



Datenblatt - Fiche technique - Data sheet

11.04.5635




ROLINE DisplayPort Kabel, DP ST - Mini DP ST, 2,0m

ROLINE Câble DisplayPort DP M - Mini DP M, 2,0m


ROLINE DisplayPort Cable, DP - Mini DP, M/M, 2 m

ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△K2	B	ECR # 110829-7 EDIT: CABLE SPEC, TITLE	08/29/11'



- NOTE:
- CABLE:UL20276 [32(7/0.08T.C)]x1P INS:FOAM-SKIN-PE+D.W(7/0.08T.C)
 +Free-edge-al-foil/Mylar|x5C+#32(7/0.08T.C)x5C INS: PP+AL/MY
 +B.D(85%)PVC JACKET; OD:5.5±0.2mm COLOR:BLACK(NK-K01).
 - CONNECTOR:
 P1:DISPLAYPORT 20P MALE W/P/CB CONTACT:15u",SHELL:NI-PLATED.
 P2:MINI DISPLAYPORT 20P MALE CONTACT:15u",SHELL:NI-PLATED.
 - SHIELD: P1:INNER MOLD MUST BE WRAPPED COPPER TO
 CONNECTOR SHELL & CABLE BRAID
 P2:COPPER-FOIL 360° SOLDERED TO CONNECTOR
 SHELL& CABLE BRAID
 - HOOD:P1:ASS'Y TYPE, COLOR:BLACK(NK-K01)
 P2:MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
 - ELECTRICAL TEST:
 <1>-100% OPEN SHORT & MIS WIRE TEST.
 <2>-CONTACT RESISTANCE 3 Ohms MAX.
 <3>-INSULATION RESISTANCE 10M Ohms MIN.
 - PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.



- 100% OPEN SHORT & MIS WIRE TEST.
- CONTACT RESISTANCE 3 Ohms MAX.
- INSULATION RESISTANCE 10M Ohms MIN.
- PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.

200-1447-3	11.04.5637-10	5000	50	10	20
200-1447-2	11.04.5636-20	3000	30	20	40
200-1447-1	11.04.5635-20	2000	30	20	40
DWG	P/N	L (mm)	T (mm)	PCS/INNER CARTON	PCS/CARTON

Tolerance Inch M/M	
X	.015 .30
.XX	.010 .10
.XXX	.005 .05
Draw	
FANNIE 08/29/11'	

Rotronic Co., LTD.

Title
DisplayPort - Mini DisplayPort Cable(V1.2)

Customer P/N

App'd	Customer: T-RAG
Scale NONE	Units M/M
Dwg No. 200-1447	REV: B
Sheet 1/1	Third Angle Projection