

PRODUCT-DETAILS

TY1000-175X

CABLE TIE 778NT 1030X9MM BLK NY HVY



General Information

Extended Product Type	TY1000-175X
Product ID	7TAG054360R0101
EAN	5415022140880
Catalog Description	CABLE TIE 778NT 1030X9MM BLK NY HVY
Long Description	Extra Heavy-Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor or Outdoor Applications, Length of 1030mm (40.55 Inches), Width of 8.76mm (0.345 Inch), Thickness of 2.16mm (0.085 Inch), Tensile Strength Rating of 780 Newtons (175 Pounds)

Ordering

EAN	5415022140880
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.045 lb 20.408 g
--------------------	---------------------

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	6 in

	152 mm
Package Level 1 Height	2 in 51 mm
Package Level 1 Depth / Length	46 in 1168 mm
Package Level 2 Units	500 piece
Package Level 2 Width	8 in 203 mm
Package Level 2 Height	8 in 203 mm
Package Level 2 Depth / Length	50 in 1270 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	12 in 304.8 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Extra Heavy Duty
Standards	UL E49405
Tensile Strength	175 lb 780 N
Thickness	0.085 in 2.16 mm
UPC	786209514011

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY1000-175X
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY1000-175X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

