

Clamps



Version:

- Heat-treated steel
- Painted
- With self-locking trapezoidal thread spindle and end safety device.
- With flat support

Art. no.	26157 020
Min./max. support plate height	42-52 mm
Diameter	50 mm
Head diameter	50 mm
Max. force range	100 kN
Centring diameter	12 mm

EAN-Code

4020772072384

