

Electronic micrometer

Non-rotating spindle

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- Non-rotating spindle

Advantage:

- Long battery life, approx. 2.4 years

Delivery:

Includes box, one battery, wrench



Art. no.	32017 393
Brand	MITUTOYO
Manufacturer Part Number	406-252-30
Display	Digital
Min./max. length measuring range	50-75 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
Measuring arrangement	Standard
Material of measuring bolt	Carbide
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	3-8 N
Error limit	6 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	60 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	1.305 kg
Product Group	3MA

EAN

494636868979 1