

## Spring balance capacity 0.0-2.5 kg

Type 7200, cable extraction 1600 mm

AUTOSTAT

### Application:

For the ergonomic support of assembly operations. Spring pullers keep tools close at hand at all times during assembly and at the same time ensure that the workplace is tidy. The spring balances are designed in such a way that each work tool is automatically pulled back to the original position after use. Suitable for lightweight tools.

### Execution:

- Housing made of extremely shock-resistant special plastic
- Cable drum is made of non-abrasive plastic
- High-strength special motive spring
- Simple load setting secured against incorrect operation
- Cable feed limitation is impact absorbing and adjustable
- The load is attached via a safe snap hook
- Suspension with screw snap hook
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, insulated suspension, shape-stabilised structure
- Working area: Cable extraction: 1600 mm, ropes in special lengths available on request

### Advantage:

- Effortless work



<b>Art. no.</b>	<b>77001 301</b>
<b>Brand</b>	AUTOSTAT
<b>Manufacturer Part Number</b>	77001301
<b>Min. load-carrying capacity</b>	0.3 kg
<b>Max. load-carrying capacity</b>	1.5 kg
<b>Type</b>	7200
<b>With automatic locking</b>	No
<b>Max. cable pull-out length</b>	1600 mm
<b>Adjustable cord length</b>	No
<b>Material of cord</b>	Steel
<b>Wire cable diameter</b>	2 mm
<b>Replaceable cord</b>	No
<b>Cord in-feed restriction</b>	Absorbs impacts, adjustable
<b>Material of cable drum</b>	Abrasion-proof plastic
<b>Suspension type</b>	Freely rotating and pivot screw karabiner hook
<b>Load attachment</b>	Karabiner hook
<b>Colour of housing</b>	Orange
<b>Material of housing</b>	Plastic
<b>Housing height</b>	134.3 mm
<b>Housing width</b>	108 mm
<b>Housing thickness</b>	36.7 mm
<b>Design</b>	Standard
<b>Height</b>	420 mm
<b>Spring design</b>	Special mainspring
<b>With overrotation protection</b>	No
<b>Spring breakage protection</b>	No
<b>Number of springs</b>	1 PCS
<b>DIN</b>	15112
<b>Gross Weight</b>	0.663 kg
<b>Product Group</b>	772

### EAN

4039247878543