



MASTER - LED HID SON-T



MAS LED SON-T IF 6Klm 34W 740 E27

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER - LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER - LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	E27		70
Nominal lifetime	70,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	50,000	Photobiological safety according to EN 62471	RG1
Lighting Technology	LED	Operating and Electrical	
Flux measurement reference	Sphere	Line Frequency	50 Hz
Light Technical		Input Frequency	50 Hz
Color Code	740 [CCT of 4000K]	Power Consumption	34 W
Luminous Flux	6,000 lm	Lamp Current (Nom)	965 mA
Luminous Efficacy (rated) (Nom)	176 lm/W	Starting Time (Nom)	0.5 s
Color Designation	Cool White (CW)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	-
Color Consistency	<6	Voltage (Nom)	68-78 V
		Inrush current at mains	-

MASTER - LED HID SON-T

Max. lamp no. on MCB B type 10A - Mains	-
Max. lamp no. on MCB B type 10A - EM ballast without Compensation Capacitor.	7
Max. lamp no. on MCB B type 10A - EM ballast with Compensation Capacitor.	8
Max. lamp no. on MCB B type 16A - Mains	-
Max. lamp no. on MCB B type 16A - EM ballast without Compensation Capacitor.	11
Max. lamp no. on MCB B type 16A - EM ballast with Compensation Capacitor.	13
Ballast Compatibility	EM

Temperature

Ambient temperature range	-30 to +45 °C
T-Case Maximum (Nom)	59 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	T60


Approval and Application

Energy Efficiency Class	C
Energy Consumption kWh/1000 h	34 kWh
EPREL Registration Number	1077795
EU RoHS compliant	Yes

Product Data

Order product name	MAS LED SON-T IF 6Klm 34W 740 E27
Full product name	MAS LED SON-T IF 6Klm 34W 740 E27
Full product code	871951444893300
Order code	929003467312
Material Nr. (12NC)	929003467312
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.250 kg
EAN/UPC - Product/Case	8719514448933
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514448940



Dimensional drawing



Product	D	C
MAS LED SON-T IF 6Klm 34W 740 E27	61 mm	200 mm


MASTER - LED HID SON-T

Photometric data




General uniform lighting - MAS LED SON-T IF 6Klm 34W 740 E27

Light Distribution Diagram - MAS LED SON-T IF 6Klm 34W 740 E27




Spectral Power Distribution Colour - MAS LED SON-T IF 6Klm 34W 740 E27

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LED SON-T IF 6Klm 34W 740 E27

MASTER - LED HID SON-T

