

CAT 5e, SF/UTP Patchkabel CAT 5e SF/UTP Patch Cord



- Außenmantel: PVC
 - Aderquerschnitt: AWG 26/7
 - Innenleiter: Kupfer (Cu)
 - Schirmung: SF/UTP (gesamt folien- und geflechtgeschirmt, paarweise ungeschirmt)
 - Transparent blau gefärbter Stecker mit Metallschirmung
 - Hauben mit Knickschutz, Zugentlastung und Rasthebelschutz
 - Steckverbinder: FCC & EN 60603-7-3
 - Litzen-Innenleiter: 0,145 +/- 0,005 mm
 - Außendurchmesser: 5,2 +/- 0,30 mm
 - Isolierung Litzen-Innenleiter: HD-PE
 - Betriebstemperaturbereich: -20 °C bis zu +60 °C
 - PoE kompatibel
- Sheath: PVC
 - Wire cross-section: AWG 26/7
 - Conductor: Copper (Cu)
 - Shielding: SF/UTP (complete foil- and braid shielding, pairs unshielded)
 - Transparent blue colored plug with metal shielding
 - Boots with kink protection, strain relief and latch protection
 - Connector: FCC & IEC 60603-3
 - Stranded wire: 0.145 +/- 0.005 mm
 - Diameter cable jacket: 5.2 +/- 0.30 mm
 - Isolation stranded wire: HD-PE
 - Operating temperature range: -20 °C up to +60 °C
 - PoE compatible

Farbe Color Länge Length	Grau Grey	Blau Blue	Schwarz Black	Grün Green	Rot Red	Gelb Yellow
0,50 m	DK-1531-005 401603212249	DK-1531-005/B 401603213703	DK-1531-005/BL 401603213710	DK-1531-005/G 401603213727	DK-1531-005/R 401603213734	DK-1531-005/Y 401603213741
1,00 m	DK-1531-010 401603213079	DK-1531-010/B 401603213758	DK-1531-010/BL 401603213765	DK-1531-010/G 401603213772	DK-1531-010/R 401603213789	DK-1531-010/Y 401603213796
2,00 m	DK-1531-020 401603213086	DK-1531-020/B 401603213802	DK-1531-020/BL 401603213826	DK-1531-020/G 401603213819	DK-1531-020/R 401603213833	DK-1531-020/Y 401603213840
3,00 m	DK-1531-030 401603213093	DK-1531-030/B 401603213857	DK-1531-030/BL 401603213871	DK-1531-030/G 401603213864	DK-1531-030/R 401603213888	DK-1531-030/Y 401603213895
5,00 m	DK-1531-050 401603213109	DK-1531-050/B 401603213901	DK-1531-050/BL 401603213918	DK-1531-050/G 401603213925	DK-1531-050/R 401603213932	DK-1531-050/Y 401603213949
7,00 m	DK-1531-070 401603213116	DK-1531-070/B	DK-1531-070/BL	DK-1531-070/G	DK-1531-070/R	DK-1531-070/Y
10,00m	DK-1531-100 401603213123	DK-1531-100/B 401603214007	DK-1531-100/BL 401603214014	DK-1531-100/G 401603214021	DK-1531-100/R 401603214038	DK-1531-100/Y 401603214045
15,00 m	DK-1531-150 401603213130	DK-1531-150/B	DK-1531-150/BL	DK-1531-150/G	DK-1531-150/R	DK-1531-150/Y
20,00 m	DK-1531-200 401603213147	DK-1531-200/B	DK-1531-200/BL	DK-1531-200/G	DK-1531-200/R	DK-1531-200/Y
30,00 m	DK-1531-300 401603213154	DK-1531-300/B	DK-1531-300/BL	DK-1531-300/G	DK-1531-300/R	DK-1531-300/Y
50,00 m	DK-1531-500	DK-1531-500/B	DK-1531-500/BL	DK-1531-500/G	DK-1531-500/R	DK-1531-500/Y

Gelb hinterlegt = Ware ab Lager verfügbar
 Yellow highlighted = Available from stock

Neutral hinterlegt = Ware auf Anfrage erhältlich
 not highlighted = Available on request

