




REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE

8P and 8P following no reinforcement.



0.2P

NOTES1:

UL Standard

1. Rated voltage/current : 150V / 4A

2. Withstanding voltage : AC1300V/1Min.

IEC Standard

1.

Pollution degree	2
Overvoltage category	II
Rate Impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	5A

NOTES2:

1. Dimension shall be interpreted per

ASME Y14.5-2009


2. Pitch : 2.5mm, Poles : N=02~12P

3. Operating temperature: -40°C~+105°C

4. Undimensioned tolerances:

Pitch range in mm	Nominal dimension	range	-	+/-
Over	Over	Over	Over	Over
6 TO 10	10 TO 30	60 TO 100	150 TO	0.1/10
6 TO 10	24 TO 30	60 TO 100	150 TO	<
±0.15/±0.20/±0.30/±0.30/±0.50/±0.70/±1.00/±1.30				
±2				

5. RoHS Compliance



15EDGVC - 2.5 - XXP - 1Y - 00A (H)

(Series No.) (Pitch) (Poles) (Color) : 1. (Grey)

2. (Blue)

3. (Black)

4. (Green)




5. (Orange)

6. (Red)

7. (Transparent)

8. (Yellow)

9. (White)



DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON® NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD.:	/	TITLE:	CUSTOMER DRAWING
CHKD.:	/	DRAWING NO.:	/
DRFT.:	/	DO NOT SCALE DRAWING	SCALE
THIRD ANGLE PROJECTION		REV	DO
		SHEET	1/1
		SCALE	1:1

