



- For solid and stranded conductors
AWG 27 up to AWG 22
- Max. wire diameter 1.5mm
- Cable diameter 6 - 12mm
- Degree of protection IP65/IP67
- Cat. 6 performance class EA
suitable for 1/10 Gigabit Ethernet
- Temperature range -40°C up to +70°C
- 750 mating cycles

Data contact plating: Au 1.27µm (50µ") over nickel

	All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.		
						Sub.		
	All rights reserved		Created by SERBANA	Inspected by PREOTU	Standardisation ROEBEN	Date 2022-10-05	State Final Release	
	Department EL PD		Title Han 3A RJ45 Hybrid 10G metal connector				Doc-Key / ECM-Nr. 100190447/UGD/002/C 50000225877	
HARTING D-32339 Espelkamp			Type TB	Number 09451151760			Rev. C	Page 1/1