




## Datasheet

# RS PRO UNCOATED BALL-LOCK STAINLESS STEEL CABLE TIES

EN



### Technical Information:

**Material:** Stainless Steel Grade 316

316 grade stainless steel, for extra corrosive environments

**Working Temp.:** -80°C to +500°C

**Description:** Metallic band and buckle

**Flammability:** Fireproof

**Other Properties:** UV-resistant

**Product Feature:** Uncoated version, for high temperature applications, quick installation.

**Applications:** Ideal for petrochemical, food industry, industries, power stations, mining, ship-building, offshore and any other aggressive environments.

## Specification

RS CODE	LENGTH		WIDTH		THICKNESS		MAX. BUNDLE DIAMETER		MIN. TENSILE STRENGTH	
	mm	inch	mm	inch	mm	inch	mm	inch	N	lbs
183-4227	100	3.9	4.6	0.18	0.26	0.010	25	1.00	1100	250
183-4228	125	4.9					31	1.23		
183-4229	150	5.9					37	1.46		
183-4230	200	7.9					50	1.97		
183-4231	360	14.2					90	3.55		
183-4232	520	20.5					130	5.13		
183-4233	680	26.8					171	6.71		
183-4234	840	33.1					211	8.29		
183-4235	1000	39.4					251	9.87		
183-4237	200	7.9	7.9	0.31	0.26	0.010	50	1.97	1500	340
183-4238	360	14.2					90	3.55		
183-4239	520	20.5					130	5.13		
183-4240	680	26.8					171	6.71		
183-4241	840	33.1					211	8.29		
183-4243	1000	39.4					251	9.87		
183-4244	360	14.2	12	0.47	0.35	0.014	90	3.55	2500-2800	568-636
183-4245	440	17.3					110	4.34		
183-4246	520	20.5					130	5.13		
183-4247	680	26.8					171	6.71		
183-4248	760	29.9					191	7.50		
183-4249	840	33.1					211	8.29		
183-4250	920	36.2					231	9.08		