


Fuses 5 x 20

Ceramic Fuses, slow-blow



Time delay (T) IEC60127-2/5

Nickel plated brass end caps

Sand filled

UL approved, E492698

SPECIFICATION:

Characteristic (time/current)	Slow-blow
Rated voltage	250 VAC/DC
Type of housing/package/case	Ceramic tube
Dimensions $\phi \times L$	5.2 x 20 mm
Breaking capacity	1500 A@ 250 VAC

PRODUCT RANGE:

Art. Nr.	Rated current
RND 170-00012	0.5 A
RND 170-00009	0.8 A
RND 170-00020	1 A
RND 170-00019	1.25 A
RND 170-00018	1.6 A
RND 170-00016	2 A
RND 170-00015	2.5 A
RND 170-00008	3.15 A
RND 170-00014	4 A
RND 170-00013	5 A
RND 170-00011	6.3 A
RND 170-00010	8 A
RND 170-00017	10 A