

Electrical plug base MHAP-PI

Part number: 197260

FESTO



Data sheet

Feature	Value
Type code	MHAP-PI
Type of mounting	Clip
Product weight	4 g
Electrical connection	Socket 2-pin
DC operating voltage range	≤60 V
Current rating	3 A
Cable length	0.5 m
Cable diameter	1 mm
Cable design	2 x 0.14 mm ²
Degree of protection	IP40
Ambient temperature	-20 °C ... 80 °C
Ambient temperature with flexible cable installation	-20 °C ... 50 °C
Note on materials	RoHS-compliant
Housing material	PA
Material of pin contacts	Tin-plated Copper
Mounting position	Any