

Product information

70 01 160

Diagonal Cutter


DIN ISO 5749


- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	70 01 160
EAN	4003773013426
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	171 g
Dimensions	160 x 50 x 13 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.0 mm
Cutting capacities hard wire (diameter)	Ø 2 mm

technical change and errors excepted





clean cutting of thin copper wires, also at the cutting edge tips