


Part number

CX 01 UF



Brief description:

female insert, housing for USB male connectors, USB female - female connectors, female insert with USB female - female connector, 1 module, modular units series MIXO


Product description		Approvals / Standards	
Model	female insert	Quality mark	 , DNV GL, BV, EAC
Version	housing for USB connectors	Conformity	Not applicable
Product type	female insert with USB female - female connector	General ordering information	
Family	MIXO series, customizable inserts	EAN13 code	8015747175036
Size	1 module	Tariff number	85369095
Technical data		Packaging Information	
Operating temperature range (min, max)	-25°C ... +80°C	Packaging length	112,00 mm
Further technical details		Packaging height	95,00 mm
Characteristics according to EN 61984	50V 0.8kV 3	Packaging width	117,00 mm
Insulation resistance	≥ 1 GΩ	Packaging weight	0,21 kg
Rated voltage according to UL/CSA	50V	Packaging volume	1,24 dm ³
UL 94 flammability rating	V-0	Packaging description	Carton box
Weight	16,00 g	Packaging quantity	10 Pcs
		Packaging EAN code	8015747175050
		Sub-packaging weight	0,02 kg
		Sub-packaging description	Plastic bag
		Sub-packaging quantity	1 Pcs
		Sub-packaging EAN barcode	8015747175067

Part number


CX 01 UF



Catalogue drawings



Catalogue drawings



Notes

CX 01 U insert:

- USB-A / USB-A Hi-Speed - 2.0 insert
- temperature range: from -25 °C to +80 °C
- 1 frame slot
- enclosures: bulkhead mounting housings, high construction housings or high construction hoods

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support