

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE
2059685



Product features

- Integrated LED spotlight, white RAL 9016, compact and minimalist design, ideal for retail, display, museum and gallery applications, die-cast aluminium body, passive cooling heatsink, beam angle: 34° medium beam, optics: Polycarbonate lens, colour temperature: 3000K warm white, total system power: 33W, total fixture output: 3060lm, luminaire efficacy: 93lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 850mA, electronic driver, dimmable via on-board potentiometer, power factor: 0.9 electrical protection: CLASS II, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, dimensions: Ø113x165x205mm, weight: 1.66kg.



PRODUCT OVERVIEW

| | |
|-----------------------------|--|
| Product name | BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE |
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Museums & Galleries, Retail |
| ETIM Class | EC001744 |
| E-number FI | 4280845 |
| Warranty | 5 years |
| Fixture luminous flux (lm) | 3060 |
| Luminaire efficacy (lm/W) | 93 |
| LOR (%) | 100 |
| Colour temperature (K) | 3000 |
| Light colour | Warm White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Beam Angle (°) | 34 |
| Photobiological Risk Group | RG1 |
| Total power consumption (W) | 33 |
| Product Voltage (V) | 240 |
| Electrical protection | Class II |
| Control gear type | Electronic ballast |
| Dimmable | Yes |
| Dimming method | 1-10V (Analogue) |
| Minimum dimming level (%) | 1 |
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Product EAN number | 5025768596850 |

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE
2059685

DATA TABLE

General data

| | |
|--|--|
| Product name | BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE |
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Museums & Galleries, Retail |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC001744 |
| E-number FI | 4280845 |
| Warranty | 5 years |

Optical data

| | |
|-----------------------------------|------------|
| Fixture luminous flux (lm) | 3060 |
| Luminaire efficacy (lm/W) | 93 |
| LOR (%) | 100 |
| Colour temperature (K) | 3000 |
| Light colour | Warm White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Adjustable chromaticity | N |
| Beam Angle (°) | 34 |
| Photobiological Risk Group | RG1 |

Electrical data

| | |
|--|--------------------|
| Total power consumption (W) | 33 |
| Mains voltage (V) | 220-240V |
| Product Voltage (V) | 240 |
| Lamp power factor | 0.9 |
| Electrical protection | Class II |
| Control gear type | Electronic ballast |
| Transformer required | Yes |
| Dimmable | Yes |
| Dimming method | 1-10V (Analogue) |
| Minimum dimming level (%) | 1 |
| Drive current (mA) | 850 |
| Inrush Current (A) | 5 |
| Inrush Duration (µs) | 50 |
| Glow Wire Test (°C) | 650 |
| Energy Efficiency Class (A->G) of contained light source | E |
| Nominal Frequency (Hz) | 50/60Hz |
| Max. Luminaires per 10A C Breaker | 52 |
| Max. Luminaires per 16A C Breaker | 85 |
| Max. Luminaires per 20A C Breaker | 104 |

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE
2059685

| | |
|-----------------------------------|----|
| Max. Luminaires per 10A B Breaker | 31 |
| Max. Luminaires per 16A B Breaker | 50 |

Lifetime data

| | |
|------------------|-------|
| Lifespan L70 B50 | 72000 |
| Lifespan L80 B20 | 72000 |
| Lifespan L90 B10 | 33000 |



Physical data

| | |
|-------------------------------|-------|
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK02 |
| Nominal Product Length (mm) | 85 |
| Nominal Product Width (mm) | 165 |
| Nominal Product Height (mm) | 205 |
| Nominal Product Diameter (mm) | 113 |
| Weight (kg) | 1.365 |

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5025768596850 |
| Packaging single length / height (cm) | 25.0 |
| Packaging single width (cm) | 19.5 |
| Packaging single depth (cm) | 20.0 |
| DUN14 (outer) | 05025768596850 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 25.0 |
| Packaging outer width (cm) | 19.5 |
| Packaging outer depth (cm) | 20.0 |

PHOTOMETRY



TECHNICAL DRAWINGS

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3 ON-BOARD DIM WHITE

2059685

