

Horizontal pull clamp

Complete with counter-holder



Application:

For quick and secure clamping on machine tables and appliances.

Execution:

- Galvanised and passivated
- Hook tempered
- Case-hardened and lubricated bearing bushes
- Rivet made of stainless steel
- Oil-resistant handle with large handle surface and soft components



Art. no.	26219 310
Brand	AMF
Manufacturer Part Number	94698
Design	Horizontal
Size	2
Max. tensile force	1.6 kN
Height	99 mm
Min./max. clamping width	42-76 mm
Hole distance	13 mm
Bore diameter	5.2 mm
Min./max. distance between baseplate fastenings	38-72 mm
Counterholder weight	12 mm
Overall height of lower handle 2	99 mm
Min./max. elongated hole spacing	19.5-23.5 mm
Distance between centre and drill hole 2	6.4 mm
Min./max. length	125-159 mm
Base pedestal width	26 mm
Width	38 mm
Gross Weight	0.147 kg
Product Group	260

EAN

4020772094690