

## Wheeled workbench, model 1504

Working height 985 mm

**GEDORE**  
WERKZEUGE FÜR'S LEBEN

### Application:

The mobile workstation with versatile options for use.

### Version:

- Large locking side section with fixed storage tray
- Basic configuration contains 10 longitudinal and 2 cross-partitions and 4 spacing boxes 1500 ED-70 K for drawers

<b>Art. no.</b>	<b>50271 030</b>
<b>Model</b>	1504 0511
<b>Number of drawers</b>	7 PCS
<b>Drawer front height</b>	5 x 67 mm, 1 x 137 mm, 1 x 207 mm
<b>Draw width (inner dimension)</b>	480 mm
<b>Drawer depth (inner dimension)</b>	400 mm
<b>Load-carrying capacity per drawer</b>	40 kg
<b>Pullout type</b>	Full extension
<b>With single pull-out safety brake</b>	No
<b>With single-locking drawers</b>	No
<b>Load-carrying capacity</b>	700 kg
<b>Dynamic load-carrying capacity</b>	500 kg
<b>Central locking</b>	Yes
<b>Lock type</b>	Cylinder lock
<b>With sliding handle</b>	No
<b>Number of fixed rollers</b>	2 PCS
<b>Number of steering rollers</b>	2 PCS
<b>With wheel lock</b>	Yes
<b>Material of wheel</b>	Solid rubber
<b>Wheel diameter</b>	125/200 mm
<b>Material of worktop</b>	Multiplex beech
<b>Material</b>	Sheet steel
<b>Body colour</b>	Traffic blue RAL 5017
<b>Colour of front</b>	Traffic blue RAL 5017
<b>Surface</b>	Powder-coated



### EAN-Code

4010886662281