

“Light strip“ LED machine light, tiltable

155, 305 or 560 mm, IP 67



Execution:

- high-performance LED in aluminium housing
- Light temperature: cold white, approx. 5500 Kelvin, high-performance chip
- 120 degree uniform illumination, anti-glare and flicker-free, low-reflection
- connection to 24 V machine controller or to 230 V via power pack
- 2 x 43 mm rubber-coated magnets each with 85 N retention force.

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use

Delivery:

including power pack



Art. no.	56886 011
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/66
Power rating	5 W
Length	155 mm
Luminous flux	600
IP protection class	IP 67
Gross Weight	0.500 kg
Product Group	5ID

EAN

4260131238666