

															
	cm	inch	TRG mm	Teilung	Anzahl TRG		HM	VM						Ø mm	Schärfwinkel °
AEG															
KES35, KS30, KS35, KS40	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ALDI															
BENZIN-KETTENSÄGE Mc.C. 839	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ALKO															
EKI 2200 / 40	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
1400E, 1500E, 2000, 2300, 25A, E125, BKS35/35 II, E1200, KE3000, KE3500, KE3500 VARIO, KE4000, KS1300, KSB1300, KSB1300B, KS SUPERLUXE, KSB SUPERDELUXE KE180/40s	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS40, BKS40II	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KB400, KB4500	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KB450, KB3500, KB3501, KB4000, KB4001, KB4500, KE1800/40S	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KE40-16/18	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KE 1600/ 40, KE1635/35, KE1750/40	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

KE1800/35	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KB35/35, KB38/40, 1750W35, 1750W40	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KB38/40 = 526-AC3107	40	16	1,3	3/8H	54	160SDEA318 160SXEA318		91PX054E 91VXL054E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
526 (AC3107 16-38), KE1800/35, AC310714-38, BKS35/35, BKS 42/45	40	16	1,3	3/8H	54	160SDEA318 160SXEA318		91PX054E 91VXL054E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA318 140SXEA318		91P050E 91PX050E 91VXL050E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KB5000	45	18	1,3	3/8H	60	180SDEA318		91P060E 91PX060E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	'325	66	160SLGK095		20BPX066E	20LPX066E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	'325	72	180SLGK095		20BPX072E	20LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
ALPINA																			
A3700	35	14	1,3	3/8H	53	140SDEA041 140SXEA041		91P053E 91PX053E 91VXL053E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
C25	25	10	1,3	3/8H	40			91PX040E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
P34, P34S,	30	12	1,1	3/8H	44			90PX044E			A1 558549		A2		23736A	Q104365 12211E	A5/70511 70511T	4,5	30
330, 380, 432, 438, EURO-35, EURO-40, EURO-45, JOLLY 40 GARDEN RANGER, PR350	30	12	1,3	3/8H	44			91P044E 91PX044E 91VXL044E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
ELETTRA 160, ELETTRA 170, PR350, P360, P390, SYNERGIE 35, SYNERGIE 40, SYNERGIE 45	30	12	1,3	3/8H	44	120SDEA318 120SXEA318		91P044E 91PX044E 91VXL044E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA074 140SXEA074		91P050E 91PX050E 91VXL050E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
A-10E, A-14E, E120, E130, E150, KS 1400B, KS 1500B	30	12	1,3	3/3H	45	120SDEA041 120SXEA041		91P045E 91PX045E 91VXL045E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
P450, P500	40	16	1,5	'325	66	168SLBK095 168SLGK095 168PXBK095		21BPX066E	21LPX066E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	'325	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Castor Happy Garden CX 35N, CX 40N	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30

Energy 1.8, P361, P371	35	14	1,3	3/8H	50	140SDEA074 140SXEA074	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Energy 2.0Q	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PR 270	25	10	1,3	3/8H	40		91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P411	40	16	1,3	325	64		95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P420, P440	40	16	1,3	325	66		95VPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P460,	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
C46, C50, P460, P480, P510	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P510	50	20	1,5	325	78	208SLBK095	21BPX078E	21LPX078E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P660, P680; P800	50	20	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
P680, P700, P800, Prof700, Prof750, Prof800	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
A40E, A45, P41, P45, Prof41, Prof45,	40	16			65		20BPX065E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T		
	45	18	1,3	325	72	180SLGK095	20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Castor Happy Garden CX 45N	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Castor Happy CX 40	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Castor CP 360	35	14	1,3	3/8H	50	140SDEA074 140SXEA074	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Castor CP 390	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Garden Ranger/Jolly 40	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Range/Jolly 35N	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Range/Jolly 40N	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Silver	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
A40, A40E, P41, P45, PROF41, PROF45	40	16	1,3	325	65		20BPX065E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T		
	45	18	1,3	325	72	180SLGK095	20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Castor CP 450	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Castor CP 500	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P700, P800, PROF-700, PROF-800, PROF-750	45	18	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25

	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E		K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
ALPINA PREMIUM																		
270	25	10	1,3	3/8H	40		91PX040E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
361	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
391Q	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
430	40	16	1,3	325	66		95VPX066E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
470	45	18	1,3	325	72		95VPX072E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
ASGATEC																		
EK1400, EK1600, EK1801, EK1840, EK2001, EK2040	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
ATIKA																		
KSH600	20	8	1,1	3/8H	33	084LNEA041	90PX033E			A1 558549		A2		23736A	Q104365 12211E	A5/70511 70511T	4,5	30
Comet KS200/40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KS 2001/40, KSC 2401/40	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS38	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 38A	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BAHR																		
KSB3940, KSE2000, KSE2150, KSI1800-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KSB 4945	45	18	1,3	325	72		95VPX072E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
BASIC																		
EKS 1800	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
EK1800	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS4640	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BESTGREEN																		
BG1900T	40		1,3	3/8H	56		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BG3840	40	16	1,5	325	66		21BPX066E	21LPX066E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
BG4245	45	18	1,3	3/8H	56		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
BG4445	45	18	1,3	325	72		20BPX072E	20LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30

BLACK & DECKER																	
GK1817, GK1817, GPC 1800	20	8	1,1	3/8H	34			90PX034E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
CS30, CS35, DN400, DN401, DN402, DN404, DN412, DN416, GK30, GK120, GK300, GK310, GK320, GK321, GK322, GK330, GK331, GK430, GK435, GK440, GK535, GK540, GK425, GK35, GK1430, GK1440, GK1630, GK1630T, 35T, 40T, GK1635TX	30	12	1,3	3/8H	44	120SDEA318 120SXEA318		91P044E 91PX044E 91VXL044E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA318 160SXEA318		91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GK 1635TX-QS	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GK1640T	40	16	1,3	3/8H	56	160SDEA318 160SXEA318		91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ALLIGATOR GK1000	10	4	1,3	1/4	42			25AP042E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BONUS																	
EKS 2500QT - 2000 Watt	40	16	1,3	3/8H	55			91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSB 35, MKS3835, GK1635TE	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSE2000S	40	16	1,3	3/8H	55	160SDEA318 160SXEA318		91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSi1800-35, KSi1800	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BOSCH																	
AKKUSÄGE 30Li	30	12	1,1	3/8H	45			90PX045E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
AKE30/17S, AKE3000, AKE35, AKE35S, AKE35/17S, AKE3500E, AKE40, AKE40S, AKE40/17S, AKE4000, AKE30/18S, AKE35/18S, AKE35/19, AKE35/19S, AKE40/19S	30	12	1,1	3/8H	45	124MLEA041		90PX045E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	35	14	1,1	3/8H	52	144MLEA041		90PX052E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	57	164MLEA041		90PX057E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
1586.7, 1586.8, AKE30B, AKE35B, AKE40B, BKE30, GKE35B, GKE35BC, GKE40BC, PKE25, PKE30B, PKE35B, PKE40B, PKE40, AKE30/19PRO, AKE35/19PRO, AKE40/19PRO, ab 2006 :AKE3000, AKE3500, AKE4000, AKE Edition, GKE35BCE, GKE40BCE	30	12	1,3	3/3H	45	120SDEA041 120SXEA041		91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BUDGET																	
BKS 1600	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS401	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS402	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BULLCRAFT																	

KSE30, KS300, KS1300B, BES1300B, KS40S, KS400S, KSE1300B	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CARREFOUR																
9097-31C005	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

CASTOR																	
P-34,P-34S,CP-34S,TR-350	30	12	1,1	3/8H	44			90PX044E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
330, CX35, 380, CX40, 423, 438, CX45, P34, P-34S, CP34-S	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ELECTRIC, E120, E130, E150, KS1400B, KS1500B	30	12	1,3	3/3H	45	120SDEA041 120SXEA041		91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ELETTRA 160, ELETTRA170	30	12	1,3	3/8H	44	120SDEA318 120SXEA318		91P044E 91PX044E 91VXL044E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA074 140SXEA074		91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
C-40,C-40E,CP-41,CP-45	40	16	1,3	3/8H	65			20BPX065E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T		
	45	18	1,3	3/8H	72	188SLBK095 188SLGK095 188PXBK095		20BPX072E	20LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP-700,CP-800	45	18	1,5	3/8	68	188SLHD009 188SFHD009		73DPX068E 73DX068E	73LPX068E 73LGX068E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208SLHD009 208SFHD009		73DPX072E 73DX072E	73LPX072E 73LGX072E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
Happy Garden CX 35N, Happy Garden CX 40N	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Happy Garden CX 45N	45	18	1,3	3/8H	60			91P060E 91PX060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Happy CX 40	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	60			91P060E 91PX060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CP 360	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CP 390	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CP 450	40	16	1,5	3/8H	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	3/8H	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP 500	45	18	1,5	3/8H	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Hi-tech1.8, CP371	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Hi-tech2.0Q	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TR270	25	10	1,3	3/8H	40			91PX040E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

CP411	40	16	1,3	325	64			95VPX064E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP440	40	16	1,3	325	66			95VPX066E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP460, CP510	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP480	45	18	1,3	325	72			95VPX072E			D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CP600	50	20	1,5	3/8	68	39450		73DPX068E 73DX068E	73LPX068E 73LGX068E		K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
CASTORAMA																			
CAST TPE 40	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CHAMPION																			
138/242/335-16	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CMI																			
CMI25ccm	30	12	1,3	3/3H	45	120SDEA041 120SXE041		91P045E 91PX045E 91VXL045E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CMI1800	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS-1800	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CMI38	40	16	1,3	3/8H	56	160SDEA041 160SXE041		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CMI 45-40	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
2040KSS Elektro,C-BKS 45,4-40, C-BUS 38	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CMI 45-40	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
COMET																			
CKS 200; KS2000/40	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CUB CADET																			
CC 1936, CC 2740	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA095		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
CC3045, 3352, 3551, 4051, 4256	33	13	1,5	325	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/8	60	168SLHK095		73DPX060E 73DX060E	73LPX060E 73LGX060E		K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	188SLHK095		73DPX068E 73DX068E	73LPX068E 73LGX068E		K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
DOLMAR																			

ES-2-A, ES-31A,ES-31, ES-33 A, ES-36A, ES-38A, PS-38 A, ES-40A,PS-34,PS-3,PS-2, PS32C, PS-36, PS-4, PS4/35	30	12	1,1	3/8H	46	124MLEA041		90PX046E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	35	14	1,1	3/8H	52	144MLEA041		90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	56	164MLEA041		90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
ES 4 A QS, ES 32A QS, ES 5 A QS, ES 37A QS, ES 41A QS	30	12	1,1	3/8H	46	124MLEA041		90PX046E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	35	14	1,1	3/8H	52	144MLEA041		90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	56	164MLEA041		90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
PS220TH, PS221TH, PS222TH	25	10	1,3	3/8H	40			91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
100, 100S, 101, 102, 103, 104, 105, 106, 108, 200, 201, 260, 275, 285, 290, 295, ES-3, ES 6 A QS, ES-30, ES-35, ES 41A QS ES-42 A, ES140, ES151A, ES152A, ES 152 A QS ES-153 A, ES160, ES161A, ES162A, ES 162 A QS, ES-163 A, ES171A, ES172A, ES 172A QS, ES-173 A, ES1600, ES 2035 A, ES2035 AP, ES 2040A, ES-2135A, ES2135 AP, ES-2140A ES, ES2140 AP, PS33, PS-34, PS35 C, PS-39ES, PS41, PS-41 QS, PS-2, PS45, PS-45 QS, PS330, PS 330 QS, PS340, PS 340 QS, PS341, PS 341 Happy Start, PS344, PS3410, PS350, PS350 C, PS350 SC, PS 390 QS, PS400, PS 400 QS, PS401,PS 401 QS Happy Start, PS3300TH, PS3400TH, PS3410 TH, PS3410 TH TLG	30	12	1,3	3/3H	46			91PX046E 91VXL046E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
110i,113,111,115i	33	13	1,3	325	56	130MPBK095 130MLBK095		95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK095 150MLBK095		95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095		95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
PS-410,PS-411, PS420, PS420 C, PS420 SC	33	13	1,3	325	56	130MPBK041 130MLBK041		95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK041 150MLBK041		95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MLBK041		95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
105,108, 111,115i, PS-460, PS4600S, PS-500, PS5000, PS5000H	33	13	1,5	325	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66			21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
PS 6400, PS 7300, PS 7900	40	16	1,5	3/8	60	168SLHD009 168SFHD009		73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	188SLHD009 188SFHD009		73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208SLHD009 208SFHD009		73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
109, 111, 112, 114, 115i/H, 116, 116SI, 117, 119, 120 SUPER/SI, 219, PS-43,	38	15	1,5	3/8	56	158SLHK153		73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		25
109, 111, 112, 114, 115i/H, 116, 116SI, 117, 119, 120 SUPER/SI, 219, PS-43,	45	18	1,5	3/8	64	188SLHK153		73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25

PS52,PS-460, PS4600S, PS5000, PS-500, PS5000H, PS5105, PS5105 H, PS6000i/H, PS630, PS6400, PS6400 H, PS6800i/H, PS7300, PS7300 H, PS7900, PS7900 H, PS9000, PS9010	50	20	1,5	3/8	72	208SLHK153	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
DO IT															
CSE 2040/code 78203, YD-KYO3-38A, YD-KY05-38A	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DYNAMAC															
DY36, DY19E	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DY51/46	45	18	1,5	3/8H	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
ECHO															
CS-285EVL, CS-290EVL, CS-300EVL, CS-302, CS-315, CS-320EVL, CS-328, CS-330EVL, CS-360EVL, E155, CS-2800, CS-2900, ECS-2000/3000/3050, CS-3400, CS-3450/4400, ECS150/1850FT, CS2600, CS3000, CS3400, CS3050, CS3500	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS-360EVL, CS-400EVL, CS-440EVL, CS-3600, CS3700, S-3700, CS-3900, CS-4000, CS-4200, CS-4010, CS-4050, CS-4400, CS-4500, CS-4510, CS-4600, CS-4601, CS-4610, CS-5000, CS5100	33	13	1,5	3/8H	56	138SLBK041 138PXBK041	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/8H	64	158SLBK041 158PXBK041	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/8H	66	168SLGK041 168PXBK041	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	3/8H	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS-60S, CS-451VL, CS-452VL, CS-500EVL, CS-500VL, CS-510EVL, CS-550EVL, CS-600EVL, CS-602VL, CS-610EVL, CS-650EVL, CS-660EVL, CS-702VL, CS750EVL, CS-750VL, CS5500	40	16	1,3	3/8	60	160SLHD176		72LPX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,3	3/8	64	180SLHD176		72LPX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,3	3/8	70	200SLHD176		72LPX070E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
CS-5501,CS-6700, CS-6701,CS-8000	40	16	1,5	3/8	60		73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	64	188SLHD176	73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
ED JOHNSON															
M1L-KW08-405-1	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EFCO															
131	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
134, 135, 114E, 116, 136, 17E, 140	30	12	1,3	3/8H	44		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49		91P049E 91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

138, 141	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
142, 146, 151, 152 ,156, 162	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
EF15E	30	12	1,1	3/8H	45		90PX045E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EF17E	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EF19E	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
147, 152	40	16	1,5	325	66	168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
170, 171, 180, 181	40	16	1,5	3/8	60	168SFHD024	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	188SLHD024 188SFHD024	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208SLHD024 208SFHD024	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	63	25	1,5	3/8	88				K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
EINHELL															
HOCHENTASTER BG-EC 620T, GE-EC 720T, GC-LC 1815T	20	8	1,1	3/8H	33	084LNEA041	90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
GC-LC 750T KIT	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EK1535, EK1540, PES30/2, PES34/2, PES34/3, PES35, PROFI, PES35/2TS, PES35/3, PES35/3TS, PES40/3, PKS35/1AV, PKS40/1AV, PES1540, PES1640, KSE1640, KSE1435, KSE2000	30	12	1,3	3/3H	45	120SDEA041 120SXE041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PES2000	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 38-35	35	14	1,3	3/8H	49	140SDEA318 140SXE0318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS1940, MKS38/41, RBK1440	40	16	1,3	3/8H	54	160SDEA318 160SXE0318	91PX054E 91VXL054E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1840, EKS 2040 P, PEK 1840 KSE2000, KSE2040WK, PKS2040WK	40	16	1,3	3/8H	57	160SDEA041 160SXE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1845	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS 35/35	35	14	1,3	3/8H	49	140SDEA318 140SXE0318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS 38/45, MKS42/45, RBK1745	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

PES 1640/1, PES 1740, PES 1840/1	40	16	1,3	3/8H	55	160SDEA318 160SXEAE318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS 1635, PKS 1840	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS45/1AV,PKS50/1AV	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
RBK4645, RBK5045, BG-PC5045	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Pro Work PEK 1840	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
REK 1840	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
RBC 4640, REK 2040WK, BG-EC1840, BG-EC2040, RG-EC2240S, REK2048, SCS2000	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
RBK 3735, BG-PC1235, BG-PC3735	35	14	1,3	3/8H	52	140SDEA041 140SXEAE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BG-PC1235, GH-PC 1535 TC	35	14	1,3	3/8H	53	140SDEA041 140SXEAE041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
RBK 4040, BG-PC4040	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ELECTROLUX															
EL1750-14, ESV1914	35	14	1,3	3/8H	50	140SDEA318 140SXEAE318	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2115	35	14	1,3	3/8H	52	140SDEA041 140SXEAE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EXPERT PERFORMANCE															
1403-002	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ERGO-TOOLS															
E-EAS620	20	8	1,1	3/8H	33		90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
E-KS2035	35	14	1,3	3/8H	52	140SDEA041 140SXEAE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FEAS6020T Hochentaster	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FEKS2040	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FEVILL															
SCS 723	40	16	1,1	3/8H	56		90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
FLEURELLE															
FEKS 2040, KSE2040	40	16	1,3	3/8H	57	160SDEA041 160SXEAE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FARMER															

MKS 350	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS360, MKS 360W	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FIVEA															
2200W	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GCS 3800	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FLO															
FLO 2000 79820	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FLO 79832, FLO 7982	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
FLORABEST															
HOCHENTASTER 550WATT, FHE550A1	25	10	1,3	3/8H	40	100SDEA041	91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FKS2000A1, FKS2000B1, FKS2000/6, FKS2000/7, FKS22000A1, FKS2200 B1, FKS2200/1, FKS200/08, FKS2200/8, FKS2200/9, FKS2200/10	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FLORASELF															
CS35, P38, 330 Elektro 1500 Watt	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
538, PE 1401	35	14	1,3	3/8H	44	140SDEA318 140SXEA318			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	49	160SDEA318 160SXEA318			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
330 Elektro, 335 Elektro, 340 Elektro	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GARDEN															
GD33, GD36, Euro35N, P360	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GD33, GD39, P390	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GD45, P450	45	18	1,5	3/25	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
GD50, P500	50	20	1,5	3/25	78		21BPX078E	21LPX078E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
GARDEN MASTER															
GM06023	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GARDENA															
CST2018-LI	20	8	1,1	3/8H	34		90PX034E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30

CST3018	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CST3519CX	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CSI 4020	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GARDOL															
HOCHENTASTER GASI 24-20	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GHH-E20 Li	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GMSE 1535	35	14	1,3	3/8H	53		91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GMSE 2245	45	18	1,5	3/25	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
GEKI 25-40 PRO	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GO/ON															
EK 1800	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PC1800 WATT, EKS1835/2	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GREENLINE															
G-36	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GREENWORKS															
HOCHENTASTER 20107	20	8	1,1	3/8H	33		90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
GRIZZLY															
Florabest FKS2200/10	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Hochentaster 550 Watt, Art-Nr: 75010036	25	10	1,3	3/8H	40	100SDEA041	91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Parkside EKS 1650	40	16	1,1	3/8H	55		90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EKS 1800-40, EKS 1800-40-i	40	16	1,1	3/8H	55		90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
BKS35N	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-14	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-32cc	30	12	1,3	3/8H	44		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-32cc	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-38cc	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-38cc, BKS 35-40cc	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 35-40cc	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 38-14	35	14	1,3	3/8H	49		91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

BKS 38-16	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 350, BKS351	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS400	35	14	1,3	3/8H	53		91P053E 91PX053E 91VXL053E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS450-8	40	16	1,5	3/25	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Comet CKS2000	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS600T	20	8	1,3	3/8H	36		91PX036E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS610T	20	8	1,3	3/8H	33	080SDEA041	91PX033E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS1600, EKS1800	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1600/7, EKS 1600/8, EKS 1600/9, EKS1835/2, EKS1835QT	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1650	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1800-40, EKS1800-40I	40	16	1,1	3/8H	55		90PX055E	A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EKS ELEKTRA 170, EKS 1700, EKS 1700-40, EKS 1800, EKS 1800-40	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ParksidePKS40/5, PKS40/5, EKS1835QT, EKS1800-40, EKS1850, EKS1850/1, EKS200/40, EKS2000/6, EKS2000/6QT, EKS2000/8, EKS2000/8QT, EKS2200QT, BKS400	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 2000, EKS 2000 QT, EKS2500/5, EKS2500, EKS2500QT, EKS2500/5, EKS2500/5QT, PKS2000/4, PKS40, PKS40/3, KS400I, KSF400TI	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS350	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P390	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS 35	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS 360, PKS 390	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS40, PKS40/3, PKS2000/4	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS40/5	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Farmer MKS360	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

KSE 400TL	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GUEDE																
GAK 600	20	8	1,1	3/8H	33	084MLEA041	90PX033E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
KS350E, KS350B	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
K400B	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
K450B	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KS500B	50	20	1,3	3/8	72	200SLHD176	72DPX072E	72LPX072E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
HANDY POWER																
HP1400TE 1400W	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HP35TT, HANDY P.35CC EPA2	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HANSEATIC																
EKS 1640	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HERKULES																
HHEK 18-35/1	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
36/35, HHEK 22-40, PKS 1840, 18/41, 39/41, P 352	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
41 / 41	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
41 / 41 AB 2003	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS 4048, P 372	40	16	1,3	325	66	160MPBK095 160MLBK095	95VPX066E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
MKS42-45	45	18	1,3	3/8H	60	180SDEA041	91P060E 91PX060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
49 / 46	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HITACHI																
CS280A, CS280B, CS350A, CS350B	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS25ECSC	25	10	1,3	1/4	60		25AP060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS25EC S	25	10	1,3	3/8H	40		91PX040E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

CS25EPB S	25	10	1,1	3/8H	40			90PX040E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
CS30EC S , CS30EGS, CS30EHS, CS30EJ, CS33EB	30	12	1,3	3/3H	45	120SDEA041 140SXEA041		91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS35EG S, CS35EH S,CS35EJ	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS33EL	33	13	1,3	325	56			95VPX056E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS33EL	33	13	1,3	325	56			20BPX056E	20LPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS38EL, CS38EK	38	15	1,3	325	64			95VPX064E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS38EL, CS38EK	38	15	1,3	325	64			20BPX064E	20LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS40EL, CS40EK	40	16	1,3	325	66			95VPX066E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS40EL,CS45EK, CS45EL	45	18			72			95VPX072E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS40EL,CS45EK, CS45EL	45	18	1,3	325	72			20BPX072E	20LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS40EM, CS40SM	40	16	1,5	325	66			21BPX066E	21LPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CS45EM	45	18	1,5	325	72			21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HM-MUELLER																	
EKS1800CE	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HOFER																	
Alko526(AC31071638)	40	16	1,3	3/8H	54	160SDEA318 160SXEA318		91PX054E 91VXL054E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HOMELITE																	
192, 200, 240/SL, 245/SL, BANDITLX30, SUPER2SL, SUPER2/2, VISUPER2SL, ELELECTRIC, XL, XL-10, XL2CC, XL2SUPER, XLTI, EL14, 205, i3350B	30	12	1,3	3/8H	48			B48 Q91VG048E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	53			91P053E 91PX053E 91VXL053E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	59			91PX059E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
250, 252, 290, 290C, 300, 340, 340C	33	13	1,5	325	57	138SLBK095 138PXBK095					D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T		
	38	15	1,5	325	65	158SLBK095 158SLGK095 158PXBK095		21BPX065E	21LPX065E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
30, 150, EZ, EZAUTO, MINI, SUPEREZAUTO, SUPERXLMINI, EZ250 VISUPERMINI, VI-123,	40	16	1,3	325	67						D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T		
30, 150, EZ, EZAUTO, MINI, SUPEREZAUTO, SUPERXLMINI, EZ250 VISUPERMINI, VI-123, VI-125, XL-76, XL100SERIES, XL250, 3850B, i3850B, 415b, 4550b	45	18	1,3	325	72	180SLGK095		20BPX072E	20LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Bandit BCS35, i3350b, CS 3314	30	12	1,3	3/3H	45	120SDEA041 120SXEA041		91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041		91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HCS3435BA	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

HCS3840BA	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HCS4245BA	45	18	1,3	3/8H	62			91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
RCS2040	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HCS 4041, HCS4041CA	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HCS 4446	46	18	1,3	3/25	72			95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
i3850b, i4150b, i4550b	40	16	1,3	3/25	66			20BPX066E	20LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72			20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CSP 3314, HCS3335, HCS3335A, HCS4014, PCN3335	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CSP 3816; CSP 4016, PCN4040	40	16	1,3	3/25	66	160SLGK095		20BPX066E	20LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
CSP 4518, HCS4545, PCN4545	45	18	1,3	3/25	72	180SLGK095		20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HCS 4040; HCS4545	40	16	1,3	3/25	66	160SLBK095		20BPX066E	20LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HOPEM																
1302, 140Z, 142Z	30	12	1,3	3/3H	45	120SDEA041 120SXE041		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
K1, K2, K3, K2SUPER	33	13	1,5	3/25	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/25	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/25	66	168SLBK095 168SLGK095 168PXBK095		21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HORNBAACH																
PWR1800CSC, PP1800TE	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HURRICANE																
HOCHENTASTER HESI750	20	8	1,3	3/8H	33	080SDEA041		91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ES2040S	40	16	1,3	3/8H	55	160SDEA318 160SXE318		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
HEKA20-40, HEKA24-40, HHEK24-40	40	16	1,3	3/8H	57	160SDEA041 160SXE041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
36/35, HEK 18-35	35	14	1,3	3/8H	52	140SDEA041 140SXE041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS 3, MKS 38/35	35	14	1,3	3/8H	49	140SDEA318 140SXE318		91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

MKS21/40	40	16	1,3	3/8H	55	160SDEA095	91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS42/45	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MS1235/1, 1235/2	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MS1235/2	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PS2000-40E	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PS40, PS400, MKS38/41	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91P054E 91VXL054E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MS2245	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
HUSQVARNA																
Hochentaster: 327P4, 327P5X, 327PT5S,	25	10	1,1	3/8H	40		90PX040E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	30	12	1,1	3/8H	45		90PX045E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
436Li, 536 Li XP, T536Li XP	25	10	1,1	3/8H	40		90PX040E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	30	12	1,1	3/8H	45		90PX045E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	35	14	1,1	3/8H	52		90PX052E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
135, 236, 334, 335XPT, 315E, 316E, 318E, 317, 317 EL, 321, 321 EL, 334, 439, T425, T435, T540XP	25	10	1,3	3/8H	40		91PX040E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
M4615	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
36, 40, 41, 45, 51, 55, 136, 141, 142E40CC , 236, 246, E1400, E1600, EL16, 340, 345, 346XP, 350, 351, 435, 440e, 445, 445e, 450e, 543XP/XPG, 545, 550XP/XPG	33	13	1,3	3/25	56	130MPBK095 130MLBK095	95VPX056E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	3/25	64	150MPBK095 150MLBK095	95VPX064E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,3	3/25	66	160MPBK095 160MLBK095	95VPX066E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72	180MPBK095 180MLBK095	95VPX072E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
33, 40P, 42, 44, 50, 133, 154, 234, 238, 242, 242XP/XPG, 246, 246XP/XPG, 254, 254XP/XPG, 257, 262, 262XP/XPG, 340, 445, 445e, 450e, 543XP/XPG, 545, 550XP/XPG, 555, 560XP/XPG, 562XP/XPG, 576XP/XPG, EL16, EL1200, EL1400, EL1500, EL1600,	33	13	1,5	3/25	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/25	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/25	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	50	20	1,5	3/25	78	208SLGK095	21BPX078E	21LPX078E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

55, 154, 254, 257, 261, 262, 262XP / XPG, 357XP, 359, 362XP / XPG, 455, 455eRancher, 545, 550, 555, 560XP/XPG,	38	15	1,5	3/8	56	158SLHK095	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	40	16	1,5	3/8	60	168SLHK095	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	64	188SLHK095	73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	39450	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208RNDK095 208SLHK095	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
61, 65, 66, 77, 162, 181, 254, 254XP/XPG, 266, 266XP, 268, 268XP, 272, 272XP/XPG, 281, 281XP, 285, 288XP, 298XP, 365, 371, 371XP/XPG, 372XP/XPG, 380, 385XP, 390XP, 390XPG, 394XP/XPG, 395XP/XPG, 480, 562XP/XPG, 576XP/XPG, 1100, 2100, 2100XP, 2101XP, 3120XP,	38	15	1,5	3/8	56	158SLHD009 158SFHD009	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	40	16	1,5	3/8	60	168SLHD009 168SFHD009	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	64		73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
IKRA															
HOCHENTASTER BAS3018, BAS3020	20	8	1,1	3/8H	33	084LNEA041	90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
TOP CRAFT EKS 1700	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
SHARK 1300, KS 1400-TS/30, 35, 40, KS 1500-T/35,40, KS 1500-TS/35, 40, KS 1600-TS/40, 45, KS1800-40CK, KS1800TS-45, EKS -30, 35, 40, MKS 35, 40	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KS 1200-B/30,35 , KS 1400-B/40	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS4135, KSE2000-35, KSI1800-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS4141	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS5146	45	18	1,5	325	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
EKS 1500-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSB3940, KSE2000, KSE2400-40, KSI2000, KSI2000-40, KSI2200	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSB 4945	45	18	1,3	325	72		95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
KSE2400-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

KSE2400, KSE2400-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSE2000-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSE2000-40, KSE2540LA	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSE2000-45, KSE2150	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSI1600-35, KSI1800, KSI1800-40	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSI1600-40, KSI1800-40, PKS 1635, PKS1840, Swing 1840, PKS 4645	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS 4240	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
JATT															
YT4653	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
YT4774	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
JENN FENG															
AC310114-35	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
JOLLY															
40 Garden ranger	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
JONSERED															
370, 380, 2036, CS2117EL,CS2121EL, 2135T, 2138	30	12	1,3	3/3H	45	120SDEA095 120SXEA095	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA095 140SXEA095	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA095	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2014, 2016, 2040, 2041, 2045, 2050, 2054, 2147, 2152	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	180MPBK095 180MLBK095	94VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
2014, 2016, 2040, 2041, 2045, 2050, 2054, 2147, 2152	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
EL1200, EL14, 45E, 49SP, 50, 51, 52E, 370, 380, 410, 420, 435, 450, 451E, 451EV, 451EVS, 452, 455, 490, 510, 520, 525, 535, 590, 2012, 2015, 2041, 2045, 2050, 2051, 2054, 2055, 2149, 2163, 2159, 2150, 2145,	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

2141, 2137, 2152	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
670,670CHAMP,670SUPER, 2063,2065,2071,2077, 2083,2094,2095, 2171, 2165, 2163	38	15	1,5	3/8	56	158SLHD009 158SFHD009	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	40	16	1,5	3/8	60	168SLHD009 168SFHD009	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	45	18	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
KING CRAFT																
EKS 1750 Jahr 2000	40	16	1,1	3/8H	55		90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30	
BKS400-2,2	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
BKS 4135	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
BKS 4141	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
BKS 5146	45	18	1,5	325	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
EKS 1600-40, EKS 1750 ab 6/2002, EKS1800- 40, KS 2000TF-40	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KS 2000TF-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KS 2000TS-40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KS 2000TS-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KSE 2000-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KSE 2000-40, KSI2000-40, KSI2200	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KSI2000-40	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KSE 2000-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
1800/40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
1920	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KINZO																
1,2 KW	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
1,5KW	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	

GAEDEN POWER 35cm	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
GARDEN POWER 1600 WATT	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
LANDSCAPE															
POSITEC LX302 2400W	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
LEROYSOMER															
TLS1412, TLS1530, TLS1614, TLS1616, TLS1635, TLS1716, S2025 SFN 1600W	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
S2027 SFN 2000W	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
LIDL															
HOCHENTASTER FLORABEST 550 WATT	25	10	1,3	3/8H	40	100SDEA041	91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Florabest FKS2200/10	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
LUX															
AKS 184/20, BAS 34/20, B-HS SET, B-HS plus Set, E-AS 710/20, A-AS 18Li/20, AKS 18Li/20, EAS 600/20, EAS 18Li20, A-HS18Li Set	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKSL 2200-40, EKS 2400-40, E-KSL- 2200/40, E-KS 2200/40L, B-KS 40,1/40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 46,4/45	45	18	1,3	3/8H	61	180SDEA041	91PX061E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS 42/45, BKS 46/45 plus, BKS 46/45, BKS 46,4/45, B-KS/45plus	45	18	1,3	325	72	310243	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
MAC ALLISTER															
Mac 2000 TEL2000W	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 2000 TE 45-2000W, NOUVEAUTE 2005	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 2150-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 2240, MEKS 2240	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 50CC	50	20			78										
Mac 38TT45	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MAKITA															
BUC122RFE	12	5	1,3	1/4	42		25AP042E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DCS34, UC3020A, UC3520A, UC4020A, EA3200S35A, EA3201S35A	30	12	1,1	3/8H	46	124MLEA041	90PX046E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	35	14	1,1	3/8H	52	144MLEA041	90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	56	164MLEA041	90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30

3500A, 4000A, DES341, DES330S, DES350, DES390, DES400, VC3000A, DES380, DES300, DES340, DES401, 400, 5012B, DCS330TH, DCS401	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BUC250RDE, BUC250Z,DCS232-T, DCS3410TH-35, DCS3500, DCS2501, DCS4610, DCS4610-35, EA3100T-25B, EA3200S-35, EA3200S-40B, EA3201S-35, UC3030A, UC3520A, UC3530AP, UC4020A, UC4030AP, UC4530A, UC4530AP	25	10	1,3	3/8H	40	100SDEA218	91PX040E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	12	1,3	3/3H	46	160SDEZ041	91PX046E 91VXL046E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DCS230T, DCS232T, EA3100T-25B	25	10	1,3	1/4	42		25AP042E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	25	10	1,3	3/8H	40	100SDEA218	91PX040E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DCS430, DCS460, DCS461, DCS500, DCS501, DCS520, DCS4300, DCS4600S, DCS4630-38, DCS5200	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
DCS-410, DCS-411, DCS430, DCS520, DCS4300, DCS4300i, DCS4301, DCS4301-38, DCS5200i, EA4300F-38C	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
UC 3000	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	12	1,3	3/3H	45		91PX046E 91VXL046E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
DCS4630-38	38	15	1,5	3/8	56	158SLHK153	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
DCS6000I, DCS6400, DCS6401-45, DCS7300, DCS7301-45, DCS7900, DCS7901-50, EA7900P-50E	38	15	1,5	3/8	56	158SLHD009 158SFHD009	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		25	
	43	17	1,5	3/8	64		73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	45	18	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
MATRIX																
HOCHENTASTER EPS850	20	8	1,3	3/8H	33	080SDEA041	91PX033E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ECS2000-400, ECS2000-400, EK 2000-400-1, EK2200-40	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EK2400-40AK	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MCS46-45	45	18	1,3	3/8H	62	180SDEA095	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PCS46-45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
SPS01-45	45	18	1,5	3/25	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
MAX BAHR															
HOCHENTASTER KSH600	25	10	1,3	3/8H	40	100SDEA041	91PX040E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MCCULLOCH															
CS340-16, CS350, CS380, CS390	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS410, CS450, CS450 elite	33	13	1,3	3/25	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	3/25	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
474, 484, 735, 740, C180, CAT35, CAT45, CALIFORNIA / ARIZON, CALIFORNIA 90, EAGERBEAVER, EUROMAC14, 16, 35, 39, 40, 41, ES22, S33, S34, 35, 36, ES26, E30ES, E35ES,E40ES, MC310, M1030E, M1035E, M1040E, 835AV, MAC1, MAC2, 2B, MAC120, MAC130, MAC140, MAC538, MAC540, MAC832, MAC835, MAC836, MAC837, MAC838, MAC839, MAC940, MM30, MM35, PROMAC7, PM6, PM7, PM36, PM310,PM320, PM330, PM340, PM360, PM364, PM370, PM374, PM380, PM400, PM470, PM474, PM480, PM484, PM510, PM930, PM730, POWERMAC6, STATESMANSENATOR, TITAN7, ProMac36, MINIMAC832/833, GTS32, ELECTRAMAC 1040, 240, Daytona 900, 3214, 3216, 3516, 3518, EB2, 6, MacCat	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PM394, PM494, MAC930, 935, Mac-Cat 839/540, 310, 330,ElectraMac 230, 235, 2000,Wildcat, Arizona, EuroMac S39/S41, Serie S450, Electramac 1035, 1030, MAC 538, MAC 14HC1,Euromac ES22, Mac12, S12, PM360, 36, 4, 730, 930, 14A/S, EM16, 10, 12, 16, 16E,	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA318 160SXEA318	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ELECTRAMAC16E, 838, Hobby star 32,	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TITAN 41,TITAN 46, 4600, 4700, 4900, 5000, Pro Mac 38/40/46, 4011, 4611, Timber bear 842/846/848,	40	16	1,3	3/25	66		20BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72		20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

1-10,10-10, 2-10, 3-10, 4-10, 5-10, 55, 57, 555, 6-10, 60, 605,610,645,650,655, 7-10, 70, 700, 80, 800, 805, 850, DE50, SP60, SP81, TIMBERBEAR610, 650, 655, TITAN50, 57, 70, 955, 1000, CP55, CP70, CP70L, PM605, PM610, PM645, PM650, PM655, PM700, PM570,	40	16	1,3	3/8	60				20LPX060E		K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T		
	50	20	1,3	3/8	71	200SLHD276					B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Electramac 230, Electramac 235, Electramac 240, Electramac 312, Electramac 312S, Electramac 314, Electramac 314S, Electramac 316, Electramac 316S, Electramac 330, Electramac 335, Electramac 340, Electramac 414, Electramac 416, Electramac ES22, Electramac ES24, Electramac ES26,	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 120	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 335, Mac 435	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 538, Mac 538E, Mac 539E, Mac 540E, Mac 542E, Mac 545, Mac 545E, Mac 833, Mac 835	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91P049E 91VXL049E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac 836, Mac 838,	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91P049E 91VXL049E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	54		91PX054E 91VXL054E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac Ca T441,	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac California, Mac California 2000 Kit, Mac California 42cc	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac Cat 436, Mac Cat438, Mac Cat 440, Mac Cat 441, Mac Cat442,	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Mac S36,	40	16	1,3	3/8H	54		91PX054E 91VXL054E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
E Promac 1900, E Promac 2200	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
MCCULLOCH																			
Promac 10-42, Promac 10-49	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E				D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E				D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
Promac 33	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E				B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30

Promac 40, Promac 40 II, Promac 46, Promac 46 II, Timber Bear 842, Timber Bear 846	40	16	1,3	325	66	160SLGK095	20BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,3	325	72	180SLGK095	20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
Promac 51, Promac 54 Deko, Promac 60, Promac 61 Deko, Promac 72	40	16	1,5	3/8	60	168SFHD024	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	45	18	1,5	3/8	68	188SLHD024 188SFHD024	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	50	20	1,5	3/8	72	208SLHD024 208SFHD024	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
4-18XT	35	14	1,3	3/8H	52	140SDEA041 140SXE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
Titanium 420, Mac 4-20 XT	40	16	1,3	3/8H	56	160SDEA041 160SXE041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
Xtreme 3,0	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
Xtreme 3,4	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
MEROX																
EK 2400-400WLK	40	16	1,3	3/8H	56	160SDEA041 160SXE041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
EKS2040/1	40	16	1,3	3/8H	57	160SDEA041 160SXE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
METABO																
5338	30	12	1,3	3/8H	44	120SDEA318 120SXE318	91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	35	14	1,3	3/8H	50	140SDEA074 140SXE074	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	40	16	1,3	3/8H	55	160SDEA074 160SXE074	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
KT1441	40	16	1,3	3/8H	57	160SDEA041 160SXE041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
1440	40	16	1,3	3/8H	59		91PX059E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
1530	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
MOGATEC																
EKS 1500-35	35	14	1,3	3/8H	52	140SDEA041 140SXE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
MKS3835	35	14	1,3	3/8H	49	140SDEA318 140SXE318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
MTD																
CC 1936, CC 2740	35	14	1,3	3/8H	52	140SDEA041 140SXE041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
CC3045, 3352, 3551, 4051, 4256	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,5	325	64		21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	

	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/8	60		73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68		73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
GCS 2 /30 T	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
MR. GARDENER															
EKS 1835/2	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS2040/1	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
NAC															
NAC 4380, NAC 4645	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
SPS 01-45	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
NAREX															
EPR-30 D-C, EPR30-20, EPR35-20, EPR-35 D-C, EPR35E, EPR-40 D-C, EPR40-20	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
NAUTAC															
135,140,144,232,236	30	12	1,3	3/8H	44		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49		91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
131	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
138	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
146	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
244, 246, 252	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
NORMA															
ROYAL NRBK5045	45	18	1,5	325	72		21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
OBI															
BKS 40	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
OBI-CMI															
1735BKS, 2040KS, 2040KSI	35	14	1,3	3/8H	49		91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2040KSS	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2115	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
OBI-DIANA															
1300-35KS, 1400-40KS	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
OBI-VARIOLUX															
2135KSE, 2140KSE, 2335BKS	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2340BKS	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
V-EKS2400	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
O.K.															
EKS 1635, OK3600	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1840	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EK 2000-400WLK	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
OLEO-MAC															
1400W, 1600w	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
OLEO-MAC															
932, 936, 940	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
935, E 1500F, E 1700F, E 1900F	30	12	1,3	3/8H	44		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
E 170F	40	16	1,3	325	64		20BPX064E	20LPX064E	B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
938, 947, 952	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
E 300F	40	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
OLEO-MAC OLYMPIK															
931	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
233, 234, 240, 244, 335, 340, 930, 935DX/X, E140F, EF160F	30	12	1,3	3/8H	44		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49		91P049E 91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
938, 941	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
940, 942, 945/A, 946, 950SUPER,950/A, 951 956, 962, E300F	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
OM-E200, 240	35	14	1,3	3/8H	50	140SDEA074 140SXEA074	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PARKSIDE															
EKS 1650, EKS 1700/40, PKS 40, PKS 40/3, EKS1700/40 ab 4/2002	40	16	1,1	3/8H	55		90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EKS1700	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS40/5, PKS 1635, PKS 1840	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1600, EKS1650, EKS 1800, EKS 2500/5, EKS 2500/5QT	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PKS200/4, PKS40, PKS40/3	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PARTNER															
1436, 1641	35	14	1,1	3/8H	52	144MLEA041	90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	56	164MLEA041	90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
335, 340, 345, 350, 351, 365, 370, 385, 390, 420, 395, P370, EL1200, EL1400, EL1435, EL1440, EL1500, P340S P351, P352, P371, P390CCS, P391, P401CCS P420CCS, P422, P470, P542e, P1535, P1550, P1840, P1850, P740, P842 Combi,	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P740	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
FORMULA 60, P842	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ES2200	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EL1450, EL1650, 405, 410, 460, 470, 510, 540, 4700, P411, P461, P462, P462CCS, P500, P511, P540H, P543, P4200, P4600, P5200, P5300	33	13	1,3	325	56	130MPBK095 130MLBK095	95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK095 150MLBK095	95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK095 180MLBK095	95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
360, 400, 450, 465, 490, 495, 500, 510, 540, 545, 605, MINIFARMERSAW, P500, P5000, P5500	33	13	1,5	325	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095	21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
P538, P538E, P1540, P1640, P538, P538E	35	14	1,3	3/8H	50	140SDEA318 140SXEA318	91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P542	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P371	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P538, P538E	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
P722T	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
Pattfield															
E-EAS610, E-EAS620	20	8	1,1	3/8H	33		90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
E-KS2035	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PE-BKS3735	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PE-BKS4645	45	18	1,3	3/8H	61	180SDEA041	91PX061E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PERFORMANCE POWER															
YT 4750	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PP1800, PP40CCEPA2, PP 41 YD-KU01-41, YT 4770, YT 4998	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PP 45 YD-KU01-45	45	18	1,3	3/8H	60	180SDEA318	91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
POWER FORCE															
AC311076	40	16	1,3	3/8H	55	160SDEA041 160SXEA041	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
POWER PLUS															
XG 1013	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
XG 64111	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PEUGEOT															
EKS1740	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TLS1630, TLS1635, TLS1635A, TLS1640, TRC1630, TRC1635, TRC1640	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PLANTIFLOR															
HOCHENTASTER ETK750	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSE2400, KSI2000	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18			62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BK 1,9-40	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BK 2,3 - 45	45	18	1,3	3/8H	60		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BK 50-45	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
POULAN															
ES300	35	14	1,1	3/8H	52	144MLEA041	90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
	40	16	1,1	3/8H	56	164MLEA041	90PX056E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
1800, 2000, 2300AV, 2300CVA, 25A, MICRO25, S25CVA, S25D, S25DA, P600, 2050, 2100, 2150, 2250, 2400, 2450, 2550, 2600, ESV1414-1450W, Woodshark 1400W, 36cc	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
1600W	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2800, 2900, 3300, 3350	33	13	1,3	3/25	56		95VPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	3/25	64		95VPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72		95VPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
200SERIES, 245, 375, 300SERIES, 306,3 400,360, 361, 3700, 3800, 400SERIES, 4000, 4200, 4400, 4800, 4900, 5200,54	33	13	1,3	3/25	56		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,3	3/8H	60	160SLHD176		72LPX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		
	50	20	1,3	3/8H	70	200SLHD176		72LPX070E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		
POWER G															
PCS 38Z	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
POWER PRUNER															
PP600	26	10	1,3	3/8H	39	100SDEA218			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
1840	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
PEK 1840	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
REMINGTON															
1300	35	14	1,3	3/8H	50		91P050E 91PX050E 91VXL050E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
RYOBI															

HOCHENTASTER RPP720, RPP1820LI	20	8	1,1	3/8H	33	084MLEA041	90PX033E			A1 558549		A2		23736A	Q104365 12211E	A5/70511 70511T	4,5	30
RCS36 AKKU	30	12	1,1	3/8H	45		90PX045E			A1 558549		A2		23736A	Q104365 12211E	A5/70511 70511T	4,5	30
35B, CS36C, CS41, CSE3330, CSE385CB, HC31, HC36, HC41, HCS31, HCS36	30	12	1,3	3/8H	44	120SDEA318 120SXEA318	91P044E 91PX044E 91VXL044E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91P049E 91VXL049E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
KS33B-SET, PCN-3335, RCS-3335C, RCS3535A, RCS3535B, RCS3535CA, RCS3535CB, RCS3535C2	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
RCS4040CA, RCS4040CB	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
ECS2040, RCS3540C, RZC3540C	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
PCN-3840, PCN-4040	40	16	1,3	3/8H	66	160SLGK041	20BPX066E	21LPX066E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
PCN-4545, RCS4446C2	45	18	1,3	3/8H	72	180SLGK041	20BPX072E	20LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
RCS4046C	46	18	1,3	3/8H	62		91PX062E 91VXL062E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
SABRE																		
31, 33, CS35, S335B, S385B, 205, 3350B	30	12	1,3	3/8H	48		B48 Q91VG048E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	53		91P053E 91PX053E 91VXL053E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	59		91PX059E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Scheppach																		
CSH2400	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
Schwarzbach																		
SEK 2000	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
SHARK																		
KS1800-40CK	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
MKS3840	40	16	1,3	3/8H	54	160SDEA318 160SXEA318	91PX054E 91VXL054E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
SHINDAIWA/SDK/ISEKI																		
YB311, YB411,150E,160, 300S, 305, 305AVZ,340, 345, 346, 350, 355, 357,360, A090B, A100C, A102, A103, A104P, A105B, A107, A110, A110P, A113, A113L, A113P, A117P, 140, A150B, A180, EYB120, EYB150, EYB180,YB291,YB301, YB391,YB395,YB401,YB491	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
370,440,488,YB377,YB495,YB691,YB501,YB6 01, YB691,YB701,360,366,377,400,415,416,420, 450, 451,500,510,560,580, A180B	33	13	1,5	3/8H	56		21BPX056E	21LPX056E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/8H	64	160SLGK041	21BPX064E	21LPX064E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/8H	72	180SLGK041	21BPX072E	21LPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30

575,577,680,695,757, YB801,YB901,YB1091	40	16	1,5	3/8	60	168SLHD009 168SFHD009	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
YB511, YB591, YB711	40	16	1,3	3/25	66	160SLGK041	20BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	3/25	72	180SLGK041	20BPX072E	20LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
SHINGU															
SP3200T,SP3200,SP3400	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
SKIL															
1605, 1606, 1607, 1620U, 1634U, 1636U	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
SOLO															
636	35	14	1,1	3/8H	52		90PX052E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,8	30
639, 641, 644, 644SP, 645, 647, 651, 654, 651SP	33	13	1,5	3/25	56	138SLBK095 138PXBK095	21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/25	64	158SLBK095 158SLGK095 158PXBK095	21BPX065E	21LPX065E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
662, 667, 670, 680, 690	38	15	1,5	3/8	56	158SLHD009 158SFHD009	73DPX056E 73DX056E	73LPX056E 73LGX056E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	40	16	1,5	3/8	60	168SLHD009 168SFHD009	73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	68	188SLHD009 188SFHD009	73DPX068E 73DX068E	73LPX068E 73LGX068E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,5	3/8	72	208SLHD009 208SFHD009	73DPX072E 73DX072E	73LPX072E 73LGX072E	K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25
635, 613, 635, 614, 620	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
600,605,Farmer	35	14	1,3	3/8H	53		91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
613-35, 630-35	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
633, 636 = Greenline 36 -39, 637, 635Eco	30	12	1,3	3/3H	45	120SDEA095 120SXEA095	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
630, 633, 636 = Greenline 36 -39, 637, 636 ab2006	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

639	35	14	1,1	3/8H	52			90PX052E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
640-40	40	16	1,3	3/8H	56	160SDEA095		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	45	18	1,5	325	64		21BPX064E	21LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
643	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
639, 644, 645, 650, 651, 651 SP, 656	33	13	1,5	325	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
656, 665, 675, 681	40	16	1,5	3/8	60	168SLHK095	73DPX060E 73DX060E	73LPX060E 73LGX060E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	45	18	1,5	3/8	68	188RNDK095	73DPX068E 73DX068E	73LPX068E 73LGX068E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	50	20	1,5	3/8	72	208RNDK095	73DPX072E 73DX072E	73LPX072E 73LGX072E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
675, 681	60	24	1,5	3/8	84	248RNDK095	73DPX084E 73DX084E	73LPX084E 73LGX084E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T			
681	70	28	1,5	3/8	92	288RNDK095		73LX092E 73LPX092E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T			
CC 1936, CC 2740	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
CC3045, 3352, 3551, 4051, 4256	33	13	1,5	325	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095	21BPX064E	21LPX064E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30	
	40	16	1,5	3/8	60	168SLHK095	73DPX060E 73DX060E	73LPX060E 73LGX060E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
	45	18	1,5	3/8	68	188RNDK095	73DPX068E 73DX068E	73LPX068E 73LGX068E		K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T	5,5	25	
Hochentaster Best Nr. 6900229	25	10			39					A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T			
STARK/SYMPRA/SYMPRATEC																	
1400,1412,1430,14830,1414,1435,14350,14835,14840,1416,1500,1600,1616,14400,16840	30	12	1,3	3/8H	44	120SDEA318 120SXEA318		91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	
STARR																	
YT4635	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30	

STAYER																			
SEC35,SEC40	35	14	1,3	3/8H	50			91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
STERWINS																			
PCS38 PN3800	35	14	1,3	3/8H	53	140SDEA041 140SXEA041		91P053E 91PX053E 91VXL053E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
PCS46 PN4600	45	18	1,5	3/25	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
STIGA																			
SE180, SP340, 930, 935, 1400	35	14	1,3	3/8H	50	140SDEA318 140SXEA318		91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
SP355	35	14	1,3	3/8H	49	140SDEA318 140SXEA318		91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
SP370	33	13	1,3	3/25	56			95VPX056E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
STIHL																			
HT56, HT70, HT75, HT101, HT131, HTE60,	25	10	1,1	3/8H	39			90PX039E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
	30	12	1,1	3/8H	44	124MLEA074		90PX044E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
009, 017, 019T, 023L, E14, E140, MS170, MS171, MS180, NS181, MS181C-BE, MS190, MS190T, MS192, MS192C-E, MS192T, MS200T,MS201T, MSE140, MSE170, MSE170C-Q, MSE170C-BQ	25	10	1,1	3/8H	39						A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
	30	12	1,1	3/8H	44	124MLEA074		90PX044E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
	35	14	1,1	3/8H	50	144MLEA074		90PX050E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
	40	16	1,1	3/8H	55			90PX055E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30		
009, 010, 011, 012, 015, 018/CQT, 020, 020T, 021/CQT,023/C/CQT, 025, AV electronic, E10, E14, E160, E180/CQT, MS170, MS180, MS190, MS190T, MS192C-E, MS192T, MS192TC-E, MS200, MS200T, MS201, MS201T, MS210, MS211, MS211C- BE, MS230, MS231, MS241, MS241C-BEM, MS241C-M, MS241C-MQ, MS241C-M VW, MS250, MSE160, MSE170, MSE180, MSE190C-Q, MSE190C-BQ, MSE200, MSE210. MSE210C-BQ, MSE230, MSE230C- BQ	30	12	1,3	3/8H	44	120SDEA074 120SXEA074		91P044E 91PX044E 91VXL044E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
	35	14	1,3	3/8H	50	140SDEA074 140SXEA074		91P050E 91PX050E 91VXL050E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
	40	16	1,3	3/8H	55	160SDEA074 160SXEA074		91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
MS230, MS231C-BE, MS250, MSE140, MSE160, MSE180, MSE200 mit Kettenschneidspannung	35	14	1,3	3/8H	51	140SDEA074 140SXEA074		91VXL051			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
	40	16	1,3	3/8H	56	160SDEA074 160SXEA074		91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30		
024, 026/CQT, 028, MS240, MS250, MS251, MS260, MS261, MS261C-BM, MS261C-M, MS261C-MQ, MS261C-M VW, MS270, MS271, MS271C-BE. MS280	33	13	1,6	3/25	56	133SLBD025		22BPX056E	22LPX056E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
	38	15	1,6	3/25	62	153SLGD025 153SFGD025		22BPX062E	22LPX062E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
	40	16	1,6	3/25	67	163SLGD025 163SFGD025		22BPX067E	22LPX067E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
	45	18	1,6	3/25	74	183SLGD025 183SFGD025		22BPX074E	22LPX074E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		
MS251C-BEQ	33	13	1,6	3/25	57			22BPX057E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30		

	38	15	1,6	325	63		22BPX063E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	
	40	16	1,6	325	68		22BPX068E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	
029, 030, 031, 032, 034, 036/QS, 038, 039, 041, 042, 044, 045, 046, 048, 056, 064, 066, E15, E20, E220/C, E220, MS290, MS291, MS291C-BEQ, MS310, MS311, MS340, MS341, MS360, MS361, MS362, MS362C-M, MS362C-MQ, MS362C-M VW, MS380, MS390, MS391, MS440, MS441, MS441C-M, MS441C-MQ, MS441C-M W, MS460, MS461, MS461-VW, MS650, MS660, MS661, MS661C-M, MS661C-M W, MS880, MSE220, MSE220C-Q	38	15	1,6	3/8	56	153SLHD025 153SFHD025	75DPX056E 75DX056E	75LPX056E 75LGX056E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	40	16	1,6	3/8	60	163SLHD025 163SFHD025	75DPX060E 75DX060E	75LPX060E 75LGX060E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,6	3/8	66	183SLHD025 183SFHD025	75DPX066E 75DX066E	75LPX066E 75LGX066E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	50	20	1,6	3/8	72	203SLHD025 203SFHD025	75DPX072E 75DX072E	75LPX072E 75LGX072E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
SWING																	
1640KS, EKS1600, EKS1640	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS1800 / 1840	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
1640 KS	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30

TALON																
AC3101-35, AC2111, AC310114-35	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
AC2108, AC2109, AC2101, AC2105	30	12	1,3	3/3H	45	120SDEA318 120SXEA318	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
AC3100	30	12	1,3	3/3H	45		91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49		91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	54		91PX054E 91VXL054E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	55	160SDEA318 160SXEA318	91P055E 91PX055E 91VXL055E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	45	18	1,3	3/8H	60		91P060E 91PX060E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
AC3102	40	16	1,3	325	66	160SLBK095	20BPX066E	21LPX066E		D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
AC3102	45	18	1,3	325	72	180SLBK095	20BPX072E	20LPX072E		B1 558488	B2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
AC3102	50	20	1,3	325	78	200SLBK095				B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CS38	35	14	1,3	3/8H	49	140SDEA318 140SXEA318	91PX049E 91VXL049E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TAS TANAKA																
TCS 2801S	25	10			40					B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TCS 3801	38	15	1,3	325	64		95VPX064E			D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
290, 300, ECS3351, ECS330, ECS3500, ECS360, ECS320, ECS3301, TCS3401, TCS3301S	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
650,ECS506,655	40	16	1,3	3/8	60	160SLHD176	72LPX060E			K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		
	45	18	1,3	3/8	64	180SLHD176	72LPX064E			K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		
	50	20	1,3	3/8	70	200SLHD176	73LPX070E			K1 558551	K2	23736A	Q104365 12211E	K5/70502 70502T		
TOP-CRAFT																
E1.7Profi	40	16			55		90PX055E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
2000	40	16			55		90PX055E			A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EKS 1700, EKS1751-40, 1800, EKS 1800-40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KSI2000-40, KSI2100, KSI 2200	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E			B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

2000	40	16	1,3	3/8H	55			91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1700	40	16			55			90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
EKS 1750	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TCK 1640 (2001)	40	16			55			90PX055E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
TCK 1640 (2001)	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
KTKS 1,8 PRO	40	16	1,3	3/8H	55	160SDEA318 160SXEA318		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TOOM																
EKS 1635, EKS 1840	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ECS2000-40	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ECS2000-40	40	16	1,3	3/8H	57			91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
EKS 1840	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
TURBO SILENT																
EKS 2040	40	16	1,3	3/8H	57	160SDEA041 160SXEA041		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS2335	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS3536, BKS3536-II	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS4041, BKS4041-II	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
BKS4245	45	18	1,3	3/8H	60	180SDEA318		91P060E 91PX060E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
UNIROPA																
PKS 35	35	14	1,3	3/8H	52			91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
VAP																
1400, 35F, 38, 40F, 44F, 52F, 530, 534, 535, 538, 60F	30	12	1,3	3/8H	44			91P044E 91PX044E 91VXL044E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	35	14	1,3	3/8H	49			91PX049E 91VXL049E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56			91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
14F, 542, 68F	33	13	1,5	3/8H	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	3/8H	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	3/8H	66	168SLBK095 168SLGK095 168PXBK095		21BPX066E	21LPX066E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30

	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
VARTOLUX															
HOCHENTASTER V-ASA 24	20	8	1,1	3/8H	33	084LNEA041	90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
HOCHENTASTER V-ASAH 40/20	20	8	1,3	3/8H	33	080SDEA041	91PX033E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2135KSE, 2140KSE, 2335BKS, BKS 40.1/40	35	14	1,3	3/8H	52		91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	57		91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2340BKS	40	16	1,3	3/8H	56		91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2340KSE, CBKS 38	40	16	1,3	3/8H	56	160SDEA041 160SXEA041	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
2340KSE, V-EKS2200-40, V-EKS2400, V-EKS 2400-40, V-BUS45, KGO-0,38/ V-EKS 2200, KGO-0,48/ V-EKS 2200-40	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
V-BKS 45	45	18	1,3	3/8H	62	180SDEA041	91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
V-BKS 42-45, V-BKS 46, V-BKS 46-45; BKS46.4/45 Vermerk: Originalkette	45	18	1,3	3/8H	61		91PX061E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
V-BKS42-45, V-BKS 46, V-BKS 46-45 Vermerk: Ersatzkette	45	18	1,3	3/8H	62		91PX062E 91VXL062E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
VICTUS															
VT36	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
VT51	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095	21BPX072E	21LPX072E	D1 558550	D2	23736A	Q104365 12211E	D5/70503 70503T	4,8	30
VT40,VT200E	40	16	1,3	3/8H	56	160SDEA074 160SXEA074	91P056E 91PX056E 91VXL056E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
WESTFALIA															
HOCHENTASTER	20	8	1,1	3/8H	33		90PX033E		A1 558549	A2	23736A	Q104365 12211E	A5/70511 70511T	4,5	30
WOLF															
CSB3835	35	14	1,3	3/8H	53	140SDEA041 140SXEA041	91P053E 91PX053E 91VXL053E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CSB4640	40	16	1,3	3/8H	55		91P055E 91PX055E 91VXL055E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CSE2035	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
CSE2240	40	16	1,3	3/8H	57	160SDEA041 160SXEA041	91P057E 91PX057E 91VXL057E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
WOODSHARK															
2275	35	14	1,3	3/8H	52	140SDEA041 140SXEA041	91P052E 91PX052E 91VXL052E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30
ZENOA															
G300T/S,G310TS,G320 AVS	30	12	1,3	3/3H	45	120SDEA041 120SXEA041	91P045E 91PX045E 91VXL045E		B1 558488	B2	23736A	Q104365 12211E	B5/70504 70504T	4	30

	35	14	1,3	3/8H	52	140SDEA041 140SXEA041		91P052E 91PX052E 91VXL052E		B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
	40	16	1,3	3/8H	56	160SDEA041 160SXEA041		91P056E 91PX056E 91VXL056E		B1 558488		B2		23736A	Q104365 12211E	B5/70504 70504T	4	30
G415AVS	33	13	1,3	325	56	130MPBK041 130MLBK041		95VPX056E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,3	325	64	150MPBK041 150MLBK041		95VPX064E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,3	325	72	180MPBK041 180MLBK041		95VPX072E		D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
G380AVS	33	13	1,5	325	56	138SXBK041		21BPX056E	21LPX056E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK041 158PXBK041		21BPX064E	21LPX064E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
G410AVS, G455AVS, G500AVS, G38, G46, G455AVS, G500AVS	33	13	1,5	325	56	138SLBK095 138PXBK095		21BPX056E	21LPX056E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	38	15	1,5	325	64	158SLBK095 158SLGK095 158PXBK095		21BPX064E	21LPX064E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	40	16	1,5	325	66	168SLBK095 168SLGK095 168PXBK095		21BPX066E	21LPX066E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
	45	18	1,5	325	72	188SLBK095 188SLGK095 188PXBK095		21BPX072E	21LPX072E	D1 558550		D2		23736A	Q104365 12211E	D5/70503 70503T	4,8	30
G621AVS	40	16	1,5	3/8	60			73DPX060E 73DX060E	73LPX060E 73LGX060E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25
	45	18	1,5	3/8	64	188SLHD176		73DPX064E 73DX064E	73LPX064E 73LGX064E	K1 558551		K2		23736A	Q104365 12211E	K5/70502 70502T	5,5	25