

Lok-it! 1200 W 80 V/32/P50

Lok-it! | Halogen lamps



Product family benefits

- Optimum use of the generated light in the spotlight



Product datasheet

Technical data

Product information

Order reference	LOK-IT! 1200W/3
-----------------	-----------------


Electrical data

Nominal voltage	80.0 V
Nominal wattage	1200.00 W

Photometrical data

Color temperature	3200 K
Color rendering index Ra	100

Dimensions & weight



Diameter	23.0 mm
Length	140.0 mm
Light center length (LCL)	84.0 mm
Illuminated field	14.7*14.5 mm ²

Lifespan

Lifespan	250 h
----------	-------

Capabilities

Burning position	Any
------------------	-----

Country specific categorizations

ANSI code	Other
Order reference	LOK-IT! 1200W/3

Product datasheet

Logistical data

EAN 10 of contained light source	4008321382795
----------------------------------	---------------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	01-04-2022
Primary Article Identifier	4008321382795
Candidate List Substance 1	No declarable substances contained
Declaration No. in SCIP database	No declarable substances contained

Product datasheet

Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (cover panel etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. Because of the heat produced only heat-resistant lamp connections (holders) may be used. Do not operate near people, or any materials that are flammable, sensitive to heat or affected by drying out. Detailed information is available on request.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321382795	Lok-it! 1200 W 80 V/32/P50	Folding carton box 1	70 mm x 70 mm x 160 mm	0.78 dm ³	178.00 g
4008321382801	Lok-it! 1200 W 80 V/32/P50	Shipping carton box 12	294 mm x 222 mm x 175 mm	11.45 dm ³	2940.81 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
