

## MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 115/230+/-10VAC OUT: :24V/5ADC


Current: 5 A

Output rating: 120 W


This power supply units meet the (EN 61000-3-2) standard for harmonic current. For any mounting position at vertical wall.

### [Link to Product](#)

#### Illustration



stay connected



Product may differ from Image

### Approvals



### Input

Input voltage	115/230 V AC $\pm$ 10 V AC
Input current	2 A (115 V AC); 1 A (230 V AC)
Input fuse (external)	3.15 AT (115 V AC); 1.6 AT (230 V AC)
Frequency	50...60 Hz

### General data

Standards	(EN 61558-2-6), (EN 62041 category I), (EN 55011 B), (EN 61000-3-2)
Mounting method	Key-hole mounting
Temperature range	-20...+60 °C, no condensation
Dimensions H x W x D	95x 96x136 mm
Fixing centers a x b x c	75x84x5.8 mm

### Output

Output voltage	24 V DC (SELV)
Ripple	max. 5 %rms
Output current (Ta 60/40 °C)	max. 5 A (115 V AC); 6 A (230 V AC)
Output fuse	10 A (automotive fuse FKS)
Output filter	LED, VDR and smoothing capacitor

### Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1